

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249854

Luminaire Tested: **LD8B80D010 ER8B809727 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249854
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B809727 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5249.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249854

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249854

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249854

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	656.5	12.5
10°-20°	1541.3	29.4
20°-30°	1684.5	32.1
30°-40°	1002.4	19.1
40°-50°	275.0	5.2
50°-60°	62.3	1.2
60°-70°	19.2	0.4
70°-80°	5.9	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3882.3	74.0
0°-40°	4884.7	93.1
0°-60°	5222.0	99.5
0°-90°	5249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7199	
5°	7084	657
15°	5531	1541
25°	3721	1685
35°	1586	1002
45°	322	275
55°	62	62
65°	20	19
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P249854

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7199.3
1°	7213.6
2°	7204.7
3°	7186.9
4°	7146.1
5°	7083.9
6°	7004.0
7°	6897.4
8°	6773.0
9°	6629.2
10°	6467.5
11°	6295.2
12°	6110.5
13°	5920.4
14°	5723.2
15°	5531.4
16°	5343.1
17°	5158.4
18°	4973.6
19°	4788.9
20°	4609.5
22.5°	4158.3
25°	3721.3
27.5°	3240.0
30°	2705.3
32.5°	2131.6
35°	1586.2
37.5°	1103.1
40°	731.8
42.5°	479.6
45°	321.5
47.5°	213.2
50°	142.1
52.5°	87.0
55°	62.2
57.5°	44.4
60°	33.7
62.5°	24.9
65°	19.5
67.5°	12.4
70°	8.9
72.5°	7.1
75°	5.3
77.5°	3.6
80°	3.6



TEST NUMBER: P249854

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	1.8
85°	1.8
87.5°	1.8
90°	0.0

(END OF REPORT)