

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250043

Luminaire Tested: **LSR8B80D010 EC8B80830 8LBN0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13946)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B80D010 EC8B80830 8LBN0WH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7478.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.66
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250043

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0WH

Luminous Intensity Polar Plot





TEST NUMBER: P250043

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76
6	92	84	79	75	90	83	78	74	82	77	74	80	76	74	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	64	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	463550
5°	448277
10°	381233
15°	290972
20°	222376
25°	172325
30°	117531
35°	69051
40°	21113
45°	8308
50°	125
55°	140
60°	160
65°	379
70°	712
75°	620
80°	462
85°	2795



TEST NUMBER: P250043

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1312.9	17.6
10°-20°	2544.1	34.0
20°-30°	2290.5	30.6
30°-40°	1133.2	15.2
40°-50°	172.4	2.3
50°-60°	7.1	0.1
60°-70°	9.1	0.1
70°-80°	3.4	0.0
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6147.4	82.2
0°-40°	7280.6	97.4
0°-60°	7460.1	99.8
0°-90°	7478.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7478.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15033	
5°	14482	###
15°	9114	2544
25°	5065	2290
35°	1834	1133
45°	190	172
55°	3	7
65°	5	9
75°	5	3
85°	8	5
90°	0	



TEST NUMBER: P250043

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBNOWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	15032.6
1°	15001.3
2°	15009.0
3°	14933.4
4°	14795.1
5°	14482.0
6°	14241.9
7°	13861.0
8°	13349.6
9°	12817.2
10°	12175.3
11°	11601.2
12°	10985.5
13°	10304.4
14°	9717.3
15°	9114.5
16°	8600.4
17°	8146.5
18°	7588.0
19°	7178.3
20°	6776.6
21°	6359.0
22°	6053.7
23°	5698.8
24°	5372.6
25°	5064.8
26°	4702.0
27°	4375.9
28°	4083.6
29°	3762.7
30°	3300.8
31°	3039.9
32°	2711.1
33°	2351.0
34°	2077.0
35°	1834.3
37.5°	1161.1
40°	524.5
42.5°	357.5
45°	190.5
47.5°	107.0
50°	2.6
52.5°	10.5
55°	2.6
57.5°	15.7



TEST NUMBER: P250043

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0WH

CANDELA DISTRIBUTION (continued):

	0°
60°	2.6
62.5°	13.1
65°	5.2
67.5°	13.1
70°	7.9
72.5°	2.6
75°	5.2
77.5°	0.0
80°	2.6
82.5°	10.5
85°	7.9
87.5°	0.0
90°	0.0

(END OF REPORT)