

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247086

Luminaire Tested: **LD8B80D010 ER8B809727 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B809727 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6207.0 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247086

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247086

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92					92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83					83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75					75			
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68					68			
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62					62			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56					56			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51					51			
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47					47			
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43					43			
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39					39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247086

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.3	5.5
10°-20°	1062.5	17.1
20°-30°	1680.3	27.1
30°-40°	1726.6	27.8
40°-50°	1071.0	17.3
50°-60°	303.6	4.9
60°-70°	20.5	0.3
70°-80°	2.8	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3082.2	49.7
0°-40°	4808.8	77.5
0°-60°	6183.4	99.6
0°-90°	6207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3464	
5°	3518	339
15°	3758	1063
25°	3685	1680
35°	2799	1727
45°	1383	1071
55°	304	304
65°	12	21
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P247086

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3463.6
2.5°	3470.3
5°	3517.8
7.5°	3573.5
10°	3626.7
12.5°	3692.4
15°	3758.2
17.5°	3795.6
20°	3793.1
22.5°	3756.5
25°	3685.0
27.5°	3555.2
30°	3354.7
32.5°	3090.9
35°	2798.9
37.5°	2468.6
40°	2110.0
42.5°	1737.2
45°	1382.8
47.5°	1053.4
50°	755.5
52.5°	508.4
55°	303.7
57.5°	156.4
60°	68.3
62.5°	27.5
65°	12.4
67.5°	7.5
70°	5.0
72.5°	3.4
75°	2.5
77.5°	1.7
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)