

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244831

Luminaire Tested: **LD8B15D010 ER8B15850 8LBM0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15850 8LBM0WMH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1479.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244831

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBM0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244831

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBM0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102				100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89				88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83				82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78				76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73				71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68				67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64				63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60				59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57				56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57251
5°	58352
10°	55635
15°	49125
20°	42571
25°	35970
30°	27033
35°	18099
40°	10136
45°	4073
50°	1410
55°	392
60°	222
65°	190
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P244831

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBM0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.4	11.9
10°-20°	429.2	29.0
20°-30°	476.3	32.2
30°-40°	301.7	20.4
40°-50°	83.7	5.7
50°-60°	9.6	0.6
60°-70°	1.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.9	73.1
0°-40°	1383.6	93.5
0°-60°	1476.9	99.9
0°-90°	1479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1857	
5°	1885	176
15°	1539	429
25°	1057	476
35°	481	302
45°	93	84
55°	7	10
65°	3	2
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	



TEST NUMBER: P244831

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBM0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1856.6
2.5°	1870.4
5°	1885.1
7.5°	1855.7
10°	1776.8
12.5°	1664.2
15°	1538.8
17.5°	1415.7
20°	1297.3
22.5°	1181.1
25°	1057.2
27.5°	912.3
30°	759.2
32.5°	610.8
35°	480.8
37.5°	363.3
40°	251.8
42.5°	156.6
45°	93.4
47.5°	53.7
50°	29.4
52.5°	14.4
55°	7.3
57.5°	5.5
60°	3.6
62.5°	1.9
65°	2.6
67.5°	1.3
70°	0.0
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244831

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBM0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)