

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249861

Luminaire Tested: **LD8B80D010 ER8B809730 8LBN0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P249861  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B809730 8LBN0H  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5553.1 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBN0H

### Luminous Intensity Polar Plot





TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBN0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBN0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	694.5	12.5
10°-20°	1630.5	29.4
20°-30°	1782.1	32.1
30°-40°	1060.5	19.1
40°-50°	290.9	5.2
50°-60°	65.9	1.2
60°-70°	20.4	0.4
70°-80°	6.2	0.1
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4107.1	74.0
0°-40°	5167.6	93.1
0°-60°	5524.4	99.5
0°-90°	5553.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5553.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7616	
5°	7494	695
15°	5852	1631
25°	3937	1782
35°	1678	1060
45°	340	291
55°	66	66
65°	21	20
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBN0H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7616.3
1°	7631.3
2°	7621.9
3°	7603.1
4°	7559.9
5°	7494.2
6°	7409.6
7°	7296.8
8°	7165.3
9°	7013.1
10°	6842.1
11°	6659.8
12°	6464.4
13°	6263.3
14°	6054.7
15°	5851.8
16°	5652.6
17°	5457.1
18°	5261.7
19°	5066.3
20°	4876.5
22.5°	4399.2
25°	3936.9
27.5°	3427.6
30°	2862.0
32.5°	2255.0
35°	1678.1
37.5°	1167.0
40°	774.2
42.5°	507.4
45°	340.1
47.5°	225.5
50°	150.3
52.5°	92.1
55°	65.8
57.5°	47.0
60°	35.7
62.5°	26.3
65°	20.7
67.5°	13.2
70°	9.4
72.5°	7.5
75°	5.6
77.5°	3.8
80°	3.8



TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBN0H

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	1.9
85°	1.9
87.5°	1.9
90°	0.0

(END OF REPORT)