

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244711

Luminaire Tested: **LD8B15D010 ER8B15940 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15940 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1330.0 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244711

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244711

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29723
5°	29125
10°	28203
15°	27822
20°	27657
25°	27308
30°	25840
35°	21310
40°	13308
45°	8556
50°	6635
55°	5107
60°	3873
65°	2517
70°	1073
75°	524
80°	231
85°	142



TEST NUMBER: P244711

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.5	6.7
10°-20°	246.2	18.5
20°-30°	366.7	27.6
30°-40°	340.6	25.6
40°-50°	160.9	12.1
50°-60°	86.4	6.5
60°-70°	34.7	2.6
70°-80°	5.5	0.4
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.4	52.7
0°-40°	1042.0	78.3
0°-60°	1289.3	96.9
0°-90°	1330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	964	
5°	941	88
15°	872	246
25°	803	367
35°	566	341
45°	196	161
55°	95	86
65°	34	35
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P244711

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	963.9
2.5°	957.2
5°	940.9
7.5°	920.1
10°	900.7
12.5°	884.8
15°	871.5
17.5°	857.8
20°	842.8
22.5°	825.5
25°	802.6
27.5°	770.3
30°	725.7
32.5°	660.3
35°	566.1
37.5°	445.9
40°	330.6
42.5°	246.2
45°	196.2
47.5°	164.0
50°	138.3
52.5°	115.3
55°	95.0
57.5°	77.3
60°	62.8
62.5°	49.1
65°	34.5
67.5°	20.3
70°	11.9
72.5°	7.1
75°	4.4
77.5°	2.7
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)