

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250355

Luminaire Tested: **LD8B150D010 ER8B150950 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B150950 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11731.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250355

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250355

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	578027
5°	568791
10°	505357
15°	416874
20°	351091
25°	296129
30°	221723
35°	125479
40°	49617
45°	13318
50°	2552
55°	0
60°	370
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250355

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBNOGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1682.7	14.3
10°-20°	3657.3	31.2
20°-30°	3926.4	33.5
30°-40°	2122.1	18.1
40°-50°	331.1	2.8
50°-60°	9.1	0.1
60°-70°	2.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9266.5	79.0
0°-40°	11388.6	97.1
0°-60°	11728.8	100.0
0°-90°	11731.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11731.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18745	
5°	18375	###
15°	13058	3657
25°	8704	3926
35°	3333	2122
45°	305	331
55°	0	9
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250355

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	18745.0
1°	18780.5
2°	18762.9
3°	18698.7
4°	18575.2
5°	18375.3
6°	18100.0
7°	17729.7
8°	17266.2
9°	16732.7
10°	16139.4
11°	15517.2
12°	14871.6
13°	14226.6
14°	13627.4
15°	13058.3
16°	12535.9
17°	12031.1
18°	11561.6
19°	11121.9
20°	10699.0
21°	10288.1
22°	9900.4
23°	9513.7
24°	9108.7
25°	8703.5
26°	8292.5
27°	7823.3
28°	7306.5
29°	6779.0
30°	6227.0
31°	5634.3
32°	5041.1
33°	4454.4
34°	3861.7
35°	3333.3
37.5°	2130.4
40°	1232.6
42.5°	657.5
45°	305.4
47.5°	164.7
50°	53.2
52.5°	6.0
55°	0.0
57.5°	6.0



TEST NUMBER: P250355

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	6.0
62.5°	0.0
65°	0.0
67.5°	6.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)