

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866672

Luminaire Tested: PRLX-2001-L-927-117L-G-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866672  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-67)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-L-927-117L-G-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 7  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3137.1 lumens  
Efficiency: N/A  
Efficacy: 33.0 lumens/watt  
Spacing Criteria (0/90/45): 1.53 / 1.53 / 1.64  
Luminous Opening: Circular (Dia: 1.58' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 95.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866672

CATALOG NUMBER: PRLX-2001-L-927-117L-G-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866672

CATALOG NUMBER: PRLX-2001-L-927-117L-G-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	101	97	93	96	93	90		92	90	87		89	87	84	82
2	98	89	81	75	95	87	80	74	83	78	73		80	75	71		77	73	69	67
3	88	77	68	62	86	75	67	61	72	66	60		70	64	59		67	62	58	55
4	80	68	58	51	78	66	58	51	64	56	50		61	55	49		59	53	49	46
5	73	60	50	43	71	59	50	43	57	49	43		55	48	42		53	47	42	39
6	68	54	44	37	66	53	44	37	51	43	37		49	42	36		47	41	36	34
7	62	48	39	33	61	47	39	32	46	38	32		44	37	32		43	37	32	30
8	58	44	35	29	56	43	35	29	42	34	28		40	33	28		39	33	28	26
9	54	40	31	26	52	39	31	25	38	31	25		37	30	25		36	30	25	23
10	50	37	28	23	49	36	28	23	35	28	23		34	27	23		33	27	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4446
5°	4473
10°	4546
15°	4645
20°	4775
25°	4940
30°	5145
35°	5421
40°	5756
45°	6033
50°	6140
55°	6163
60°	6082
65°	5844
70°	5476
75°	4989
80°	4357
85°	3425

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 55°  
 Luminance: 6163 cd/sqm

TEST NUMBER: P866672

CATALOG NUMBER: PRLX-2001-L-927-117L-G-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	2.5
10°-20°	232.5	7.4
20°-30°	378.7	12.1
30°-40°	509.9	16.3
40°-50°	598.8	19.1
50°-60°	576.0	18.4
60°-70°	446.8	14.2
70°-80°	250.7	8.0
80°-90°	65.7	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	689.2	22.0
0°-40°	1199.2	38.2
0°-60°	2373.9	75.7
0°-90°	3137.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3137.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	813	
5°	815	78
15°	821	233
25°	819	379
35°	812	510
45°	780	599
55°	647	576
65°	452	447
75°	236	251
85°	55	66
90°	0	

TEST NUMBER: P866672

CATALOG NUMBER: PRLX-2001-L-927-117L-G-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	813.2
2.5°	814.1
5°	815.1
7.5°	817.9
10°	818.9
12.5°	819.8
15°	820.7
17.5°	820.7
20°	820.7
22.5°	819.8
25°	818.9
27.5°	817.0
30°	815.1
32.5°	814.1
35°	812.3
37.5°	810.4
40°	806.6
42.5°	799.1
45°	780.3
47.5°	753.9
50°	721.9
52.5°	685.2
55°	646.6
57.5°	603.3
60°	556.3
62.5°	505.4
65°	451.8
67.5°	399.1
70°	342.6
72.5°	289.9
75°	236.2
77.5°	184.5
80°	138.4
82.5°	94.1
85°	54.6
87.5°	23.5
90°	0.0



TEST NUMBER: P866672  
 CATALOG NUMBER: PRLX-2001-L-927-117L-G-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.90	20.62	19.26	20.93	21.25	18.90	20.62	19.26	20.93	21.25
	3H	20.72	22.28	21.10	22.61	22.97	20.72	22.28	21.10	22.61	22.97
	4H	21.38	22.85	21.78	23.20	23.57	21.38	22.85	21.78	23.20	23.57
	6H	21.84	23.21	22.25	23.57	23.96	21.84	23.21	22.25	23.57	23.96
	8H	21.98	23.29	22.41	23.68	24.08	21.98	23.29	22.41	23.68	24.08
	12H	22.07	23.33	22.50	23.71	24.14	22.07	23.33	22.50	23.71	24.14
4H	2H	19.56	21.03	19.95	21.38	21.75	19.56	21.03	19.95	21.38	21.75
	3H	21.59	22.83	22.00	23.23	23.63	21.59	22.83	22.00	23.23	23.63
	4H	22.37	23.50	22.80	23.91	24.34	22.37	23.50	22.80	23.91	24.34
	6H	22.96	23.94	23.41	24.38	24.84	22.96	23.94	23.41	24.38	24.84
	8H	23.15	24.07	23.60	24.51	24.97	23.15	24.07	23.60	24.51	24.97
	12H	23.27	24.11	23.75	24.58	25.05	23.27	24.11	23.75	24.58	25.05
8H	4H	22.69	23.61	23.14	24.05	24.51	22.69	23.61	23.14	24.05	24.51
	6H	23.38	24.15	23.88	24.64	25.11	23.38	24.15	23.88	24.64	25.11
	8H	23.64	24.33	24.14	24.83	25.31	23.64	24.33	24.14	24.83	25.31
	12H	23.83	24.44	24.33	24.93	25.49	23.83	24.44	24.33	24.93	25.49
12H	4H	22.72	23.55	23.20	24.03	24.49	22.72	23.55	23.20	24.03	24.49
	6H	23.44	24.13	23.94	24.63	25.12	23.44	24.13	23.94	24.63	25.12
	8H	23.74	24.36	24.25	24.84	25.40	23.74	24.36	24.25	24.84	25.40