

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866732

Luminaire Tested: PRLX-2001-L-930-117L-L-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Pentalux
Catalog Number: PRLX-2001-L-930-117L-L-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8843.6 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 95.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866732

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866732

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		80	76	73	71
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		66	62	58	56
6	78	67	59	53	76	66	58	53	64	58	53		62	57	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56	51	47	45
8	68	56	48	43	67	55	48	43	54	48	43		53	47	43		52	47	43	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	41	36	46	40	36		46	40	36		45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25656
5°	25583
10°	25302
15°	24942
20°	24513
25°	24019
30°	23363
35°	22522
40°	21439
45°	20057
50°	18355
55°	11643
60°	4041
65°	1017
70°	177
75°	192
80°	220
85°	251

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20057 cd/sqm

TEST NUMBER: P866732

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.6	5.0
10°-20°	1242.0	14.0
20°-30°	1831.7	20.7
30°-40°	2106.2	23.8
40°-50°	1996.8	22.6
50°-60°	1095.4	12.4
60°-70°	116.0	1.3
70°-80°	9.6	0.1
80°-90°	4.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3515.3	39.8
0°-40°	5621.6	63.6
0°-60°	8713.8	98.5
0°-90°	8843.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8843.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4693	
5°	4662	442
15°	4407	1242
25°	3982	1832
35°	3375	2106
45°	2594	1997
55°	1222	1095
65°	79	116
75°	9	10
85°	4	4
90°	0	

TEST NUMBER: P866732

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	4693.0
2.5°	4687.9
5°	4661.8
7.5°	4616.4
10°	4558.0
12.5°	4488.5
15°	4407.0
17.5°	4315.3
20°	4213.6
22.5°	4102.8
25°	3982.0
27.5°	3847.0
30°	3701.0
32.5°	3543.9
35°	3374.7
37.5°	3194.4
40°	3004.1
42.5°	2804.7
45°	2594.2
47.5°	2379.7
50°	2158.2
52.5°	1773.5
55°	1221.6
57.5°	698.9
60°	369.6
62.5°	192.4
65°	78.6
67.5°	15.1
70°	11.1
72.5°	10.1
75°	9.1
77.5°	8.1
80°	7.0
82.5°	6.0
85°	4.0
87.5°	2.0
90°	0.0

TEST NUMBER: P866732

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.57	17.93	16.94	18.24	18.56	16.57	17.93	16.94	18.24	18.56
	3H	16.45	17.64	16.83	17.97	18.33	16.45	17.64	16.83	17.97	18.33
	4H	16.38	17.48	16.78	17.83	18.22	16.38	17.48	16.78	17.83	18.22
	6H	16.30	17.32	16.72	17.69	18.08	16.30	17.32	16.72	17.69	18.08
	8H	16.26	17.22	16.69	17.61	18.02	16.26	17.22	16.69	17.61	18.02
	12H	16.22	17.14	16.65	17.52	17.95	16.22	17.14	16.65	17.52	17.95
4H	2H	16.40	17.51	16.81	17.86	18.24	16.40	17.51	16.81	17.86	18.24
	3H	16.28	17.17	16.69	17.57	17.97	16.28	17.17	16.69	17.57	17.97
	4H	16.20	16.98	16.63	17.40	17.84	16.20	16.98	16.63	17.40	17.84
	6H	16.12	16.79	16.58	17.24	17.71	16.12	16.79	16.58	17.24	17.71
	8H	16.06	16.69	16.53	17.14	17.61	16.06	16.69	16.53	17.14	17.61
	12H	16.01	16.57	16.50	17.06	17.53	16.01	16.57	16.50	17.06	17.53
8H	4H	16.06	16.69	16.53	17.14	17.61	16.06	16.69	16.53	17.14	17.61
	6H	15.95	16.47	16.45	16.97	17.45	15.95	16.47	16.45	16.97	17.45
	8H	15.89	16.36	16.41	16.88	17.37	15.89	16.36	16.41	16.88	17.37
	12H	15.84	16.26	16.35	16.76	17.33	15.84	16.26	16.35	16.76	17.33
12H	4H	16.01	16.57	16.49	17.05	17.52	16.01	16.57	16.49	17.05	17.52
	6H	15.88	16.36	16.41	16.87	17.36	15.88	16.36	16.41	16.87	17.36
	8H	15.84	16.26	16.35	16.76	17.33	15.84	16.26	16.35	16.76	17.33