

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866733

Luminaire Tested: PRLX-2001-L-930-117L-L-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866733  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-77)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-L-930-117L-L-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,  
TAPERED DRUM WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 7  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9349.9 lumens  
Efficiency: N/A  
Efficacy: 98.2 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.26  
Luminous Opening: Circular (Dia: 1.58' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 95.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866733

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866733

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		87	84	81	80
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		68	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	63	57	52		62	56	52		60	55	51	50
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42		52	47	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35		45	39	35		44	39	35	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26966
5°	26837
10°	26471
15°	26025
20°	25527
25°	24961
30°	24272
35°	23396
40°	22301
45°	20867
50°	19075
55°	12104
60°	4801
65°	1837
70°	1111
75°	1212
80°	1363
85°	1518

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20867 cd/sqm

TEST NUMBER: P866733

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	463.0	5.0
10°-20°	1295.9	13.9
20°-30°	1904.7	20.4
30°-40°	2188.6	23.4
40°-50°	2079.4	22.2
50°-60°	1152.9	12.3
60°-70°	179.9	1.9
70°-80°	60.4	0.6
80°-90°	25.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3663.5	39.2
0°-40°	5852.1	62.6
0°-60°	9084.5	97.2
0°-90°	9349.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9349.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4933	
5°	4890	463
15°	4598	1296
25°	4138	1905
35°	3506	2189
45°	2699	2079
55°	1270	1153
65°	142	180
75°	57	60
85°	24	25
90°	0	

TEST NUMBER: P866733

CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4932.7
2.5°	4924.6
5°	4890.4
7.5°	4839.0
10°	4768.5
12.5°	4691.0
15°	4598.3
17.5°	4496.6
20°	4387.8
22.5°	4270.0
25°	4138.1
27.5°	3999.1
30°	3845.0
32.5°	3679.9
35°	3505.6
37.5°	3321.3
40°	3125.0
42.5°	2920.5
45°	2699.0
47.5°	2484.5
50°	2242.8
52.5°	1830.9
55°	1269.9
57.5°	772.4
60°	439.1
62.5°	260.8
65°	142.0
67.5°	77.5
70°	69.5
72.5°	63.4
75°	57.4
77.5°	51.4
80°	43.3
82.5°	34.2
85°	24.2
87.5°	12.1
90°	0.0



TEST NUMBER: P866733  
 CATALOG NUMBER: PRLX-2001-L-930-117L-L-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.07	18.45	17.44	18.76	19.08	17.07	18.45	17.44	18.76	19.08
	3H	17.01	18.22	17.39	18.55	18.91	17.01	18.22	17.39	18.55	18.91
	4H	16.99	18.11	17.39	18.46	18.84	16.99	18.11	17.39	18.46	18.84
	6H	16.97	18.00	17.39	18.37	18.77	16.97	18.00	17.39	18.37	18.77
	8H	16.96	17.94	17.39	18.33	18.73	16.96	17.94	17.39	18.33	18.73
	12H	16.95	17.88	17.38	18.27	18.70	16.95	17.88	17.38	18.27	18.70
4H	2H	16.94	18.07	17.35	18.42	18.80	16.94	18.07	17.35	18.42	18.80
	3H	16.91	17.82	17.32	18.22	18.62	16.91	17.82	17.32	18.22	18.62
	4H	16.90	17.71	17.34	18.13	18.57	16.90	17.71	17.34	18.13	18.57
	6H	16.93	17.62	17.39	18.07	18.53	16.93	17.62	17.39	18.07	18.53
	8H	16.93	17.58	17.40	18.02	18.49	16.93	17.58	17.40	18.02	18.49
	12H	16.93	17.51	17.42	17.99	18.47	16.93	17.51	17.42	17.99	18.47
8H	4H	16.81	17.46	17.28	17.91	18.38	16.81	17.46	17.28	17.91	18.38
	6H	16.85	17.39	17.36	17.88	18.37	16.85	17.39	17.36	17.88	18.37
	8H	16.87	17.36	17.39	17.87	18.37	16.87	17.36	17.39	17.87	18.37
	12H	16.91	17.35	17.43	17.84	18.41	16.91	17.35	17.43	17.84	18.41
12H	4H	16.78	17.35	17.26	17.83	18.31	16.78	17.35	17.26	17.83	18.31
	6H	16.81	17.30	17.33	17.81	18.30	16.81	17.30	17.33	17.81	18.30
	8H	16.86	17.30	17.37	17.79	18.36	16.86	17.30	17.37	17.79	18.36