

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866844

Luminaire Tested: PRLX-2001-L-935-83L-L-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866844  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-79)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Pentalux  
Catalog Number: PRLX-2001-L-935-83L-L-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,  
TAPERED DRUM WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6486.1 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27  
Luminous Opening: Circular (Dia: 1.58' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 64.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866844

CATALOG NUMBER: PRLX-2001-L-935-83L-L-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866844

CATALOG NUMBER: PRLX-2001-L-935-83L-L-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		80	76	73	71
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		66	62	58	56
6	78	67	59	53	76	66	58	53	64	58	53		62	57	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56	51	47	45
8	68	56	48	43	67	55	48	43	54	48	43		53	47	43		52	47	43	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	41	36	46	40	36		46	40	36		45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18816
5°	18763
10°	18557
15°	18293
20°	17978
25°	17616
30°	17135
35°	16518
40°	15724
45°	14710
50°	13462
55°	8539
60°	2964
65°	745
70°	129
75°	139
80°	164
85°	188

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14710 cd/sqm

TEST NUMBER: P866844

CATALOG NUMBER: PRLX-2001-L-935-83L-L-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	323.9	5.0
10°-20°	910.9	14.0
20°-30°	1343.4	20.7
30°-40°	1544.8	23.8
40°-50°	1464.5	22.6
50°-60°	803.4	12.4
60°-70°	85.0	1.3
70°-80°	7.0	0.1
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2578.2	39.8
0°-40°	4123.0	63.6
0°-60°	6390.9	98.5
0°-90°	6486.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6486.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3442	
5°	3419	324
15°	3232	911
25°	2920	1343
35°	2475	1545
45°	1903	1465
55°	896	803
65°	58	85
75°	7	7
85°	3	3
90°	0	

TEST NUMBER: P866844

CATALOG NUMBER: PRLX-2001-L-935-83L-L-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3441.9
2.5°	3438.2
5°	3419.0
7.5°	3385.8
10°	3342.9
12.5°	3292.0
15°	3232.1
17.5°	3164.9
20°	3090.3
22.5°	3009.1
25°	2920.5
27.5°	2821.5
30°	2714.4
32.5°	2599.2
35°	2475.1
37.5°	2342.9
40°	2203.3
42.5°	2057.0
45°	1902.7
47.5°	1745.3
50°	1582.8
52.5°	1300.7
55°	895.9
57.5°	512.6
60°	271.1
62.5°	141.1
65°	57.6
67.5°	11.1
70°	8.1
72.5°	7.4
75°	6.6
77.5°	5.9
80°	5.2
82.5°	4.4
85°	3.0
87.5°	1.5
90°	0.0



TEST NUMBER: P866844  
 CATALOG NUMBER: PRLX-2001-L-935-83L-L-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.49	16.85	15.86	17.17	17.48	15.49	16.85	15.86	17.17	17.48
	3H	15.37	16.56	15.75	16.89	17.26	15.37	16.56	15.75	16.89	17.26
	4H	15.30	16.41	15.70	16.76	17.14	15.30	16.41	15.70	16.76	17.14
	6H	15.23	16.24	15.64	16.61	17.00	15.23	16.24	15.64	16.61	17.00
	8H	15.19	16.14	15.62	16.53	16.94	15.19	16.14	15.62	16.53	16.94
	12H	15.14	16.06	15.58	16.44	16.87	15.14	16.06	15.58	16.44	16.87
4H	2H	15.33	16.43	15.73	16.78	17.16	15.33	16.43	15.73	16.78	17.16
	3H	15.20	16.09	15.62	16.49	16.90	15.20	16.09	15.62	16.49	16.90
	4H	15.12	15.90	15.55	16.32	16.77	15.12	15.90	15.55	16.32	16.77
	6H	15.04	15.72	15.50	16.16	16.63	15.04	15.72	15.50	16.16	16.63
	8H	14.98	15.62	15.45	16.06	16.53	14.98	15.62	15.45	16.06	16.53
	12H	14.94	15.50	15.42	15.98	16.45	14.94	15.50	15.42	15.98	16.45
8H	4H	14.98	15.61	15.45	16.06	16.53	14.98	15.61	15.45	16.06	16.53
	6H	14.88	15.40	15.38	15.89	16.37	14.88	15.40	15.38	15.89	16.37
	8H	14.81	15.28	15.33	15.80	16.29	14.81	15.28	15.33	15.80	16.29
	12H	14.76	15.19	15.27	15.68	16.25	14.76	15.19	15.27	15.68	16.25
12H	4H	14.93	15.49	15.42	15.97	16.45	14.93	15.49	15.42	15.97	16.45
	6H	14.81	15.28	15.33	15.80	16.29	14.81	15.28	15.33	15.80	16.29
	8H	14.76	15.18	15.27	15.68	16.25	14.76	15.18	15.27	15.68	16.25