

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866869

Luminaire Tested: PRLX-2001-L-940-133L-L-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-77)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Pentalux
Catalog Number: PRLX-2001-L-940-133L-L-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11548.8 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.26
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 111.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866869

CATALOG NUMBER: PRLX-2001-L-940-133L-L-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866869

CATALOG NUMBER: PRLX-2001-L-940-133L-L-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		87	84	81	80
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		68	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	63	57	52		62	56	52		60	55	51	50
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42		52	47	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33308
5°	33149
10°	32697
15°	32145
20°	31531
25°	30831
30°	29980
35°	28898
40°	27546
45°	25774
50°	23560
55°	14951
60°	5929
65°	2269
70°	1371
75°	1498
80°	1684
85°	1875

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25774 cd/sqm

TEST NUMBER: P866869

CATALOG NUMBER: PRLX-2001-L-940-133L-L-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	571.9	5.0
10°-20°	1600.6	13.9
20°-30°	2352.7	20.4
30°-40°	2703.3	23.4
40°-50°	2568.4	22.2
50°-60°	1424.1	12.3
60°-70°	222.3	1.9
70°-80°	74.6	0.6
80°-90°	31.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4525.1	39.2
0°-40°	7228.5	62.6
0°-60°	11221.0	97.2
0°-90°	11548.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11548.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6093	
5°	6040	572
15°	5680	1601
25°	5111	2353
35°	4330	2703
45°	3334	2568
55°	1569	1424
65°	175	222
75°	71	75
85°	30	31
90°	0	

TEST NUMBER: P866869

CATALOG NUMBER: PRLX-2001-L-940-133L-L-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	6092.7
2.5°	6082.8
5°	6040.5
7.5°	5977.0
10°	5890.0
12.5°	5794.2
15°	5679.7
17.5°	5554.1
20°	5419.8
22.5°	5274.2
25°	5111.3
27.5°	4939.6
30°	4749.3
32.5°	4545.3
35°	4330.1
37.5°	4102.5
40°	3859.9
42.5°	3607.4
45°	3333.7
47.5°	3068.8
50°	2770.2
52.5°	2261.4
55°	1568.6
57.5°	954.1
60°	542.3
62.5°	322.2
65°	175.4
67.5°	95.8
70°	85.8
72.5°	78.4
75°	70.9
77.5°	63.4
80°	53.5
82.5°	42.3
85°	29.9
87.5°	14.9
90°	0.0

TEST NUMBER: P866869

CATALOG NUMBER: PRLX-2001-L-940-133L-L-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.81	19.18	18.17	19.50	19.81	17.81	19.18	18.17	19.50	19.81
	3H	17.75	18.95	18.12	19.28	19.65	17.75	18.95	18.12	19.28	19.65
	4H	17.72	18.85	18.12	19.20	19.58	17.72	18.85	18.12	19.20	19.58
	6H	17.71	18.74	18.12	19.11	19.50	17.71	18.74	18.12	19.11	19.50
	8H	17.70	18.67	18.13	19.06	19.47	17.70	18.67	18.13	19.06	19.47
	12H	17.69	18.62	18.12	19.00	19.43	17.69	18.62	18.12	19.00	19.43
4H	2H	17.68	18.80	18.08	19.15	19.53	17.68	18.80	18.08	19.15	19.53
	3H	17.65	18.55	18.06	18.95	19.36	17.65	18.55	18.06	18.95	19.36
	4H	17.64	18.44	18.07	18.86	19.30	17.64	18.44	18.07	18.86	19.30
	6H	17.66	18.36	18.13	18.80	19.27	17.66	18.36	18.13	18.80	19.27
	8H	17.66	18.31	18.13	18.76	19.23	17.66	18.31	18.13	18.76	19.23
	12H	17.67	18.24	18.15	18.73	19.20	17.67	18.24	18.15	18.73	19.20
8H	4H	17.55	18.20	18.02	18.64	19.11	17.55	18.20	18.02	18.64	19.11
	6H	17.59	18.12	18.09	18.62	19.10	17.59	18.12	18.09	18.62	19.10
	8H	17.61	18.09	18.13	18.61	19.10	17.61	18.09	18.13	18.61	19.10
	12H	17.65	18.08	18.16	18.58	19.15	17.65	18.08	18.16	18.58	19.15
12H	4H	17.51	18.08	18.00	18.57	19.04	17.51	18.08	18.00	18.57	19.04
	6H	17.54	18.03	18.07	18.54	19.04	17.54	18.03	18.07	18.54	19.04
	8H	17.60	18.03	18.11	18.53	19.10	17.60	18.03	18.11	18.53	19.10