

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866882

Luminaire Tested: PRLX-2001-L-940-15L-G-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-66)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-940-15L-G-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 596.8 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.52
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 16.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866882

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866882

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72		80	75	71		77	73	69	67
3	88	77	68	62	86	75	67	61	72	66	60		70	64	59		67	62	58	55
4	80	68	59	51	78	66	58	51	64	56	50		61	55	50		59	54	49	47
5	74	60	51	44	72	59	50	44	57	49	43		55	48	43		53	47	42	40
6	68	54	45	38	66	53	44	38	51	43	37		49	42	37		48	41	37	34
7	63	49	40	33	61	48	39	33	46	38	33		45	38	32		43	37	32	30
8	58	44	35	29	57	44	35	29	42	35	29		41	34	29		40	33	29	27
9	54	40	32	26	53	40	32	26	39	31	26		38	31	26		37	30	26	24
10	51	37	29	24	50	37	29	24	36	28	23		35	28	23		34	28	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	948
5°	951
10°	955
15°	961
20°	969
25°	980
30°	995
35°	1020
40°	1055
45°	1087
50°	1104
55°	1108
60°	1102
65°	1083
70°	1045
75°	1001
80°	951
85°	941

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 1109 cd/sqm

TEST NUMBER: P866882

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.5	2.8
10°-20°	48.0	8.0
20°-30°	75.0	12.6
30°-40°	95.9	16.1
40°-50°	108.2	18.1
50°-60°	103.8	17.4
60°-70°	82.7	13.9
70°-80°	50.2	8.4
80°-90°	16.6	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	139.5	23.4
0°-40°	235.4	39.4
0°-60°	447.3	75.0
0°-90°	596.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	173	
5°	173	17
15°	170	48
25°	162	75
35°	153	96
45°	141	108
55°	116	104
65°	84	83
75°	47	50
85°	15	17
90°	0	

TEST NUMBER: P866882

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	173.4
2.5°	173.4
5°	173.3
7.5°	173.0
10°	172.0
12.5°	171.0
15°	169.8
17.5°	168.2
20°	166.5
22.5°	164.6
25°	162.4
27.5°	160.1
30°	157.7
32.5°	155.3
35°	152.9
37.5°	150.3
40°	147.8
42.5°	144.6
45°	140.6
47.5°	135.6
50°	129.8
52.5°	123.5
55°	116.3
57.5°	108.7
60°	100.8
62.5°	92.4
65°	83.7
67.5°	74.8
70°	65.4
72.5°	56.4
75°	47.4
77.5°	38.7
80°	30.2
82.5°	22.4
85°	15.0
87.5°	8.6
90°	0.0



TEST NUMBER: P866882
 CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.77	14.48	13.14	14.80	15.11	12.77	14.48	13.14	14.80	15.11
	3H	14.73	16.29	15.11	16.61	16.97	14.73	16.29	15.11	16.61	16.97
	4H	15.49	16.96	15.89	17.31	17.68	15.49	16.96	15.89	17.31	17.68
	6H	16.09	17.46	16.50	17.82	18.21	16.09	17.46	16.50	17.82	18.21
	8H	16.31	17.62	16.73	18.00	18.40	16.31	17.62	16.73	18.00	18.40
	12H	16.48	17.73	16.91	18.12	18.54	16.48	17.73	16.91	18.12	18.54
4H	2H	13.46	14.93	13.86	15.28	15.65	13.46	14.93	13.86	15.28	15.65
	3H	15.64	16.89	16.05	17.28	17.68	15.64	16.89	16.05	17.28	17.68
	4H	16.54	17.67	16.97	18.08	18.51	16.54	17.67	16.97	18.08	18.51
	6H	17.28	18.27	17.73	18.71	19.16	17.28	18.27	17.73	18.71	19.16
	8H	17.56	18.49	18.02	18.93	19.39	17.56	18.49	18.02	18.93	19.39
	12H	17.79	18.63	18.27	19.10	19.57	17.79	18.63	18.27	19.10	19.57
8H	4H	16.91	17.83	17.36	18.27	18.74	16.91	17.83	17.36	18.27	18.74
	6H	17.79	18.57	18.28	19.05	19.52	17.79	18.57	18.28	19.05	19.52
	8H	18.16	18.85	18.66	19.36	19.84	18.16	18.85	18.66	19.36	19.84
	12H	18.49	19.11	18.99	19.59	20.15	18.49	19.11	18.99	19.59	20.15
12H	4H	16.96	17.80	17.44	18.27	18.74	16.96	17.80	17.44	18.27	18.74
	6H	17.87	18.57	18.38	19.07	19.56	17.87	18.57	18.38	19.07	19.56
	8H	18.31	18.93	18.81	19.42	19.97	18.31	18.93	18.81	19.42	19.97