

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866908

Luminaire Tested: PRLX-2001-L-940-83L-L-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866908  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-79)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-L-940-83L-L-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6771.2 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27  
Luminous Opening: Circular (Dia: 1.58' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 64.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866908

CATALOG NUMBER: PRLX-2001-L-940-83L-L-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866908

CATALOG NUMBER: PRLX-2001-L-940-83L-L-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		80	76	73	71
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		66	62	58	56
6	78	67	59	53	76	66	58	53	64	58	53		62	57	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56	51	47	45
8	68	56	48	43	67	55	48	43	54	48	43		53	47	43		52	47	43	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	41	36	46	40	36		46	40	36		45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	19644
5°	19588
10°	19373
15°	19098
20°	18769
25°	18391
30°	17888
35°	17244
40°	16415
45°	15357
50°	14054
55°	8915
60°	3094
65°	777
70°	136
75°	146
80°	170
85°	194

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15357 cd/sqm

TEST NUMBER: P866908

CATALOG NUMBER: PRLX-2001-L-940-83L-L-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	338.1	5.0
10°-20°	951.0	14.0
20°-30°	1402.5	20.7
30°-40°	1612.7	23.8
40°-50°	1528.9	22.6
50°-60°	838.7	12.4
60°-70°	88.8	1.3
70°-80°	7.3	0.1
80°-90°	3.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2691.6	39.8
0°-40°	4304.3	63.6
0°-60°	6671.9	98.5
0°-90°	6771.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6771.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3593	
5°	3569	338
15°	3374	951
25°	3049	1402
35°	2584	1613
45°	1986	1529
55°	935	839
65°	60	89
75°	7	7
85°	3	3
90°	0	

TEST NUMBER: P866908

CATALOG NUMBER: PRLX-2001-L-940-83L-L-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3593.3
2.5°	3589.4
5°	3569.4
7.5°	3534.7
10°	3489.9
12.5°	3436.7
15°	3374.3
17.5°	3304.1
20°	3226.2
22.5°	3141.4
25°	3048.9
27.5°	2945.6
30°	2833.7
32.5°	2713.5
35°	2583.9
37.5°	2445.9
40°	2300.2
42.5°	2147.5
45°	1986.3
47.5°	1822.1
50°	1652.4
52.5°	1357.9
55°	935.3
57.5°	535.1
60°	283.0
62.5°	147.3
65°	60.1
67.5°	11.6
70°	8.5
72.5°	7.7
75°	6.9
77.5°	6.2
80°	5.4
82.5°	4.6
85°	3.1
87.5°	1.5
90°	0.0



TEST NUMBER: P866908  
 CATALOG NUMBER: PRLX-2001-L-940-83L-L-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.64	17.00	16.01	17.32	17.63	15.64	17.00	16.01	17.32	17.63
	3H	15.52	16.71	15.90	17.04	17.41	15.52	16.71	15.90	17.04	17.41
	4H	15.45	16.56	15.85	16.91	17.29	15.45	16.56	15.85	16.91	17.29
	6H	15.38	16.39	15.79	16.76	17.15	15.38	16.39	15.79	16.76	17.15
	8H	15.33	16.29	15.76	16.68	17.09	15.33	16.29	15.76	16.68	17.09
	12H	15.29	16.21	15.73	16.59	17.02	15.29	16.21	15.73	16.59	17.02
4H	2H	15.48	16.58	15.88	16.93	17.31	15.48	16.58	15.88	16.93	17.31
	3H	15.35	16.24	15.77	16.64	17.05	15.35	16.24	15.77	16.64	17.05
	4H	15.27	16.05	15.70	16.47	16.92	15.27	16.05	15.70	16.47	16.92
	6H	15.19	15.87	15.65	16.31	16.78	15.19	15.87	15.65	16.31	16.78
	8H	15.13	15.76	15.60	16.21	16.68	15.13	15.76	15.60	16.21	16.68
	12H	15.09	15.65	15.57	16.13	16.60	15.09	15.65	15.57	16.13	16.60
8H	4H	15.13	15.76	15.60	16.21	16.68	15.13	15.76	15.60	16.21	16.68
	6H	15.02	15.55	15.53	16.04	16.52	15.02	15.55	15.53	16.04	16.52
	8H	14.96	15.43	15.48	15.95	16.44	14.96	15.43	15.48	15.95	16.44
	12H	14.91	15.33	15.42	15.83	16.40	14.91	15.33	15.42	15.83	16.40
12H	4H	15.08	15.64	15.57	16.12	16.60	15.08	15.64	15.57	16.12	16.60
	6H	14.96	15.43	15.48	15.94	16.44	14.96	15.43	15.48	15.94	16.44
	8H	14.91	15.33	15.42	15.83	16.40	14.91	15.33	15.42	15.83	16.40