

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865893

Luminaire Tested: PRLX-2001-M-927-07L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-927-07L-G-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 240.8 lumens
Efficiency: N/A
Efficacy: 29.4 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.49
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865893

CATALOG NUMBER: PRLX-2001-M-927-07L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P865893

CATALOG NUMBER: PRLX-2001-M-927-07L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91		94	91	88		90	88	86	84
2	99	90	83	78	96	88	82	77	85	79	75		82	77	73		79	75	72	69
3	90	79	71	64	87	77	70	63	74	68	62		72	66	61		69	64	60	58
4	82	70	61	54	80	68	60	53	66	59	53		63	57	52		61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45		57	50	45		55	49	44	42
6	69	56	46	40	67	55	46	40	53	45	39		51	44	39		50	43	39	37
7	64	50	41	35	62	49	41	35	48	40	35		46	40	34		45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31		42	36	31		41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	28		39	32	27		38	32	27	25
10	52	39	30	25	51	38	30	25	37	30	25		36	29	25		35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	646
5°	647
10°	650
15°	652
20°	654
25°	657
30°	663
35°	678
40°	699
45°	716
50°	721
55°	707
60°	677
65°	637
70°	573
75°	492
80°	396
85°	243

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 50°
 Luminance: 721 cd/sqm

TEST NUMBER: P865893

CATALOG NUMBER: PRLX-2001-M-927-07L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.2	3.0
10°-20°	21.0	8.7
20°-30°	32.4	13.5
30°-40°	41.0	17.0
40°-50°	45.9	19.1
50°-60°	42.6	17.7
60°-70°	31.3	13.0
70°-80°	16.2	6.7
80°-90°	3.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	60.6	25.2
0°-40°	101.7	42.2
0°-60°	190.1	78.9
0°-90°	240.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	76	
5°	76	7
15°	74	21
25°	70	32
35°	65	41
45°	60	46
55°	48	43
65°	32	31
75°	15	16
85°	2	3
90°	0	

TEST NUMBER: P865893

CATALOG NUMBER: PRLX-2001-M-927-07L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	76.1
2.5°	76.1
5°	76.0
7.5°	75.8
10°	75.4
12.5°	75.1
15°	74.2
17.5°	73.4
20°	72.4
22.5°	71.3
25°	70.2
27.5°	69.0
30°	67.7
32.5°	66.6
35°	65.4
37.5°	64.3
40°	63.1
42.5°	61.6
45°	59.7
47.5°	57.3
50°	54.6
52.5°	51.4
55°	47.8
57.5°	43.9
60°	39.9
62.5°	35.8
65°	31.7
67.5°	27.4
70°	23.1
72.5°	19.2
75°	15.0
77.5°	11.5
80°	8.1
82.5°	5.0
85°	2.5
87.5°	0.7
90°	0.0

TEST NUMBER: P865893

CATALOG NUMBER: PRLX-2001-M-927-07L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.20	12.86	11.56	13.18	13.49	11.20	12.86	11.56	13.18	13.49
	3H	12.84	14.34	13.21	14.67	15.03	12.84	14.34	13.21	14.67	15.03
	4H	13.38	14.80	13.78	15.15	15.52	13.38	14.80	13.78	15.15	15.52
	6H	13.73	15.04	14.14	15.41	15.80	13.73	15.04	14.14	15.41	15.80
	8H	13.81	15.06	14.23	15.45	15.85	13.81	15.06	14.23	15.45	15.85
	12H	13.84	15.05	14.27	15.43	15.86	13.84	15.05	14.27	15.43	15.86
4H	2H	11.80	13.22	12.20	13.57	13.95	11.80	13.22	12.20	13.57	13.95
	3H	13.64	14.83	14.05	15.23	15.63	13.64	14.83	14.05	15.23	15.63
	4H	14.29	15.37	14.73	15.78	16.22	14.29	15.37	14.73	15.78	16.22
	6H	14.75	15.68	15.20	16.12	16.58	14.75	15.68	15.20	16.12	16.58
	8H	14.86	15.73	15.32	16.17	16.64	14.86	15.73	15.32	16.17	16.64
	12H	14.92	15.70	15.39	16.18	16.65	14.92	15.70	15.39	16.18	16.65
8H	4H	14.55	15.42	15.01	15.86	16.33	14.55	15.42	15.01	15.86	16.33
	6H	15.08	15.81	15.58	16.30	16.77	15.08	15.81	15.58	16.30	16.77
	8H	15.24	15.89	15.75	16.40	16.88	15.24	15.89	15.75	16.40	16.88
	12H	15.33	15.91	15.84	16.40	16.96	15.33	15.91	15.84	16.40	16.96
12H	4H	14.56	15.35	15.04	15.83	16.30	14.56	15.35	15.04	15.83	16.30
	6H	15.11	15.76	15.62	16.27	16.75	15.11	15.76	15.62	16.27	16.75
	8H	15.30	15.88	15.81	16.37	16.93	15.30	15.88	15.81	16.37	16.93