

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865904

Luminaire Tested: PRLX-2001-M-927-15L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-49)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-927-15L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1051.3 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865904

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865904

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	86	90	86	84	87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42	52	47	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4689
5°	4672
10°	4611
15°	4527
20°	4427
25°	4319
30°	4199
35°	4061
40°	3908
45°	3736
50°	3512
55°	2478
60°	782
65°	54
70°	37
75°	36
80°	39
85°	39

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3736 cd/sqm

TEST NUMBER: P865904

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	4.9
10°-20°	145.2	13.8
20°-30°	212.3	20.2
30°-40°	245.1	23.3
40°-50°	239.8	22.8
50°-60°	143.9	13.7
60°-70°	11.2	1.1
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	409.4	38.9
0°-40°	654.5	62.3
0°-60°	1038.2	98.8
0°-90°	1051.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1051.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	553	
5°	548	52
15°	515	145
25°	461	212
35°	392	245
45°	311	240
55°	168	144
65°	3	11
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P865904

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	552.6
2.5°	551.9
5°	548.4
7.5°	542.7
10°	535.1
12.5°	526.4
15°	515.3
17.5°	503.5
20°	490.2
22.5°	476.1
25°	461.3
27.5°	445.3
30°	428.5
32.5°	410.7
35°	392.0
37.5°	373.0
40°	352.8
42.5°	333.4
45°	311.3
47.5°	289.3
50°	266.0
52.5°	228.4
55°	167.5
57.5°	98.6
60°	46.1
62.5°	18.3
65°	2.7
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.1
77.5°	1.1
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0



TEST NUMBER: P865904
 CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.84	13.21	12.20	13.52	13.84	11.84	13.21	12.20	13.52	13.84
	3H	11.71	12.92	12.09	13.25	13.61	11.71	12.92	12.09	13.25	13.61
	4H	11.65	12.76	12.05	13.11	13.50	11.65	12.76	12.05	13.11	13.50
	6H	11.57	12.60	11.99	12.97	13.36	11.57	12.60	11.99	12.97	13.36
	8H	11.53	12.50	11.96	12.89	13.30	11.53	12.50	11.96	12.89	13.30
	12H	11.49	12.42	11.92	12.80	13.23	11.49	12.42	11.92	12.80	13.23
4H	2H	11.65	12.76	12.05	13.12	13.50	11.65	12.76	12.05	13.12	13.50
	3H	11.53	12.42	11.94	12.83	13.23	11.53	12.42	11.94	12.83	13.23
	4H	11.44	12.24	11.88	12.66	13.10	11.44	12.24	11.88	12.66	13.10
	6H	11.37	12.05	11.83	12.50	12.96	11.37	12.05	11.83	12.50	12.96
	8H	11.31	11.95	11.78	12.40	12.87	11.31	11.95	11.78	12.40	12.87
	12H	11.26	11.83	11.75	12.31	12.79	11.26	11.83	11.75	12.31	12.79
8H	4H	11.31	11.95	11.78	12.39	12.86	11.31	11.95	11.78	12.39	12.86
	6H	11.20	11.73	11.70	12.22	12.71	11.20	11.73	11.70	12.22	12.71
	8H	11.13	11.61	11.66	12.13	12.62	11.13	11.61	11.66	12.13	12.62
	12H	11.08	11.52	11.60	12.01	12.58	11.08	11.52	11.60	12.01	12.58
12H	4H	11.26	11.82	11.74	12.31	12.78	11.26	11.82	11.74	12.31	12.78
	6H	11.13	11.61	11.65	12.13	12.62	11.13	11.61	11.65	12.13	12.62
	8H	11.08	11.51	11.60	12.01	12.58	11.08	11.51	11.60	12.01	12.58