

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865906

Luminaire Tested: PRLX-2001-M-927-15L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865906  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-48)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-M-927-15L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
TAPERED DRUM WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1135.3 lumens  
Efficiency: N/A  
Efficacy: 81.1 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.27  
Luminous Opening: Circular (Dia: 1.27' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865906

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865906

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	85		89	86	83		86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	71	70
4	89	79	72	66	87	78	71	66	76	70	65		73	68	64		71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	55
6	77	65	57	52	75	64	57	52	63	56	51		61	55	51		60	54	50	49
7	72	60	52	46	70	59	52	46	57	51	46		56	50	46		55	49	45	44
8	67	55	47	42	65	54	47	42	53	46	42		52	46	41		51	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38		48	42	38		47	41	37	36
10	59	47	39	35	58	46	39	35	45	39	34		44	39	34		44	38	34	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4986
5°	4964
10°	4890
15°	4781
20°	4657
25°	4529
30°	4397
35°	4255
40°	4098
45°	3915
50°	3693
55°	2765
60°	1091
65°	297
70°	256
75°	275
80°	298
85°	292

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3915 cd/sqm

TEST NUMBER: P865906

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	4.9
10°-20°	153.4	13.5
20°-30°	223.0	19.6
30°-40°	256.8	22.6
40°-50°	251.7	22.2
50°-60°	159.9	14.1
60°-70°	23.3	2.1
70°-80°	8.8	0.8
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	431.5	38.0
0°-40°	688.3	60.6
0°-60°	1099.9	96.9
0°-90°	1135.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1135.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	588	
5°	583	55
15°	544	153
25°	484	223
35°	411	257
45°	326	252
55°	187	160
65°	15	23
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P865906

CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	587.6
2.5°	586.9
5°	582.7
7.5°	575.8
10°	567.5
12.5°	557.2
15°	544.2
17.5°	531.7
20°	515.7
22.5°	501.6
25°	483.7
27.5°	467.4
30°	448.7
32.5°	430.5
35°	410.7
37.5°	390.9
40°	369.9
42.5°	349.8
45°	326.2
47.5°	304.1
50°	279.7
52.5°	243.6
55°	186.9
57.5°	119.1
60°	64.3
62.5°	32.4
65°	14.8
67.5°	10.7
70°	10.3
72.5°	9.5
75°	8.4
77.5°	7.2
80°	6.1
82.5°	4.6
85°	3.0
87.5°	1.5
90°	0.0



TEST NUMBER: P865906  
 CATALOG NUMBER: PRLX-2001-M-927-15L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.89	14.29	13.25	14.60	14.92	12.89	14.29	13.25	14.60	14.92
	3H	12.82	14.05	13.20	14.38	14.75	12.82	14.05	13.20	14.38	14.75
	4H	12.80	13.94	13.20	14.29	14.67	12.80	13.94	13.20	14.29	14.67
	6H	12.77	13.82	13.19	14.19	14.59	12.77	13.82	13.19	14.19	14.59
	8H	12.76	13.75	13.19	14.14	14.55	12.76	13.75	13.19	14.14	14.55
	12H	12.74	13.69	13.17	14.07	14.50	12.74	13.69	13.17	14.07	14.50
4H	2H	12.73	13.87	13.13	14.22	14.61	12.73	13.87	13.13	14.22	14.61
	3H	12.69	13.61	13.10	14.02	14.42	12.69	13.61	13.10	14.02	14.42
	4H	12.68	13.50	13.11	13.92	14.36	12.68	13.50	13.11	13.92	14.36
	6H	12.69	13.40	13.15	13.84	14.31	12.69	13.40	13.15	13.84	14.31
	8H	12.68	13.34	13.15	13.79	14.26	12.68	13.34	13.15	13.79	14.26
	12H	12.67	13.26	13.16	13.74	14.22	12.67	13.26	13.16	13.74	14.22
8H	4H	12.59	13.25	13.05	13.70	14.17	12.59	13.25	13.05	13.70	14.17
	6H	12.61	13.15	13.11	13.65	14.13	12.61	13.15	13.11	13.65	14.13
	8H	12.61	13.11	13.13	13.62	14.11	12.61	13.11	13.13	13.62	14.11
	12H	12.62	13.07	13.14	13.56	14.13	12.62	13.07	13.14	13.56	14.13
12H	4H	12.55	13.14	13.03	13.62	14.09	12.55	13.14	13.03	13.62	14.09
	6H	12.56	13.06	13.08	13.57	14.06	12.56	13.06	13.08	13.57	14.06
	8H	12.59	13.04	13.10	13.53	14.10	12.59	13.04	13.10	13.53	14.10