

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250317

Luminaire Tested: **LD8B90D010 ER8B90850 8LBN0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250317  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B90D010 ER8B90850 8LBN0GPH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7740.0 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 86.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250317

CATALOG NUMBER: LD8B90D010 ER8B90850 8LBN0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250317

CATALOG NUMBER: LD8B90D010 ER8B90850 8LBN0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	381377
5°	375281
10°	333429
15°	275052
20°	231647
25°	195383
30°	146290
35°	82791
40°	32735
45°	8787
50°	1684
55°	0
60°	241
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250317

CATALOG NUMBER: LD8B90D010 ER8B90850 8LBN0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1110.2	14.3
10°-20°	2413.1	31.2
20°-30°	2590.6	33.5
30°-40°	1400.2	18.1
40°-50°	218.4	2.8
50°-60°	6.0	0.1
60°-70°	1.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6113.9	79.0
0°-40°	7514.1	97.1
0°-60°	7738.5	100.0
0°-90°	7740.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7740.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12368	
5°	12124	###
15°	8616	2413
25°	5742	2591
35°	2199	1400
45°	202	218
55°	0	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250317

CATALOG NUMBER: LD8B90D010 ER8B90850 8LBN0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12367.8
1°	12391.2
2°	12379.6
3°	12337.2
4°	12255.8
5°	12123.8
6°	11942.2
7°	11697.9
8°	11392.0
9°	11040.1
10°	10648.6
11°	10238.1
12°	9812.1
13°	9386.6
14°	8991.2
15°	8615.8
16°	8271.1
17°	7938.0
18°	7628.2
19°	7338.1
20°	7059.1
21°	6788.0
22°	6532.2
23°	6277.1
24°	6009.9
25°	5742.5
26°	5471.3
27°	5161.7
28°	4820.8
29°	4472.7
30°	4108.5
31°	3717.5
32°	3326.1
33°	2939.0
34°	2547.9
35°	2199.3
37.5°	1405.6
40°	813.2
42.5°	433.8
45°	201.5
47.5°	108.7
50°	35.1
52.5°	3.9
55°	0.0
57.5°	3.9



TEST NUMBER: P250317

CATALOG NUMBER: LD8B90D010 ER8B90850 8LBN0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	3.9
62.5°	0.0
65°	0.0
67.5°	3.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)