

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865953

Luminaire Tested: PRLX-2001-M-927-75L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-927-75L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5634.6 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865953

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P865953

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55
6	77	65	58	52	75	65	57	52	63	56	51	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	46	42	52	46	42	51	45	41	40
9	63	51	43	38	62	50	43	38	49	42	38	48	42	38	47	42	38	36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	35	44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24934
5°	24785
10°	24400
15°	23873
20°	23268
25°	22683
30°	22003
35°	21271
40°	20511
45°	19594
50°	18440
55°	13176
60°	4910
65°	1299
70°	1275
75°	1374
80°	1486
85°	1480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19594 cd/sqm

TEST NUMBER: P865953

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.2	4.9
10°-20°	765.5	13.6
20°-30°	1114.6	19.8
30°-40°	1283.7	22.8
40°-50°	1257.6	22.3
50°-60°	772.3	13.7
60°-70°	105.1	1.9
70°-80°	44.0	0.8
80°-90°	16.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2155.4	38.3
0°-40°	3439.1	61.0
0°-60°	5469.0	97.1
0°-90°	5634.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5634.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2938	
5°	2910	275
15°	2717	766
25°	2422	1115
35°	2053	1284
45°	1633	1258
55°	891	772
65°	65	105
75°	42	44
85°	15	17
90°	0	

TEST NUMBER: P865953

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2938.2
2.5°	2932.5
5°	2909.6
7.5°	2875.4
10°	2831.6
12.5°	2780.2
15°	2717.4
17.5°	2652.7
20°	2576.6
22.5°	2502.4
25°	2422.5
27.5°	2334.9
30°	2245.5
32.5°	2150.4
35°	2053.3
37.5°	1952.4
40°	1851.6
42.5°	1745.0
45°	1632.7
47.5°	1518.6
50°	1396.8
52.5°	1200.8
55°	890.6
57.5°	553.8
60°	289.3
62.5°	140.8
65°	64.7
67.5°	53.3
70°	51.4
72.5°	47.6
75°	41.9
77.5°	36.2
80°	30.4
82.5°	22.8
85°	15.2
87.5°	7.6
90°	0.0

TEST NUMBER: P865953
 CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.00	19.39	18.36	19.71	20.02	18.00	19.39	18.36	19.71	20.02
	3H	17.94	19.17	18.32	19.50	19.86	17.94	19.17	18.32	19.50	19.86
	4H	17.92	19.06	18.32	19.41	19.79	17.92	19.06	18.32	19.41	19.79
	6H	17.91	18.95	18.32	19.32	19.71	17.91	18.95	18.32	19.32	19.71
	8H	17.89	18.88	18.32	19.27	19.68	17.89	18.88	18.32	19.27	19.68
	12H	17.88	18.82	18.31	19.21	19.64	17.88	18.82	18.31	19.21	19.64
4H	2H	17.83	18.97	18.24	19.33	19.71	17.83	18.97	18.24	19.33	19.71
	3H	17.81	18.73	18.22	19.13	19.53	17.81	18.73	18.22	19.13	19.53
	4H	17.81	18.62	18.24	19.04	19.49	17.81	18.62	18.24	19.04	19.49
	6H	17.83	18.54	18.29	18.98	19.45	17.83	18.54	18.29	18.98	19.45
	8H	17.83	18.49	18.30	18.93	19.40	17.83	18.49	18.30	18.93	19.40
	12H	17.82	18.41	18.31	18.89	19.37	17.82	18.41	18.31	18.89	19.37
8H	4H	17.72	18.38	18.19	18.83	19.30	17.72	18.38	18.19	18.83	19.30
	6H	17.76	18.30	18.26	18.80	19.28	17.76	18.30	18.26	18.80	19.28
	8H	17.77	18.27	18.29	18.78	19.27	17.77	18.27	18.29	18.78	19.27
	12H	17.79	18.24	18.30	18.73	19.30	17.79	18.24	18.30	18.73	19.30
12H	4H	17.68	18.27	18.17	18.75	19.22	17.68	18.27	18.17	18.75	19.22
	6H	17.71	18.21	18.23	18.72	19.21	17.71	18.21	18.23	18.72	19.21
	8H	17.75	18.20	18.27	18.69	19.26	17.75	18.20	18.27	18.69	19.26