

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865958

Luminaire Tested: PRLX-2001-M-930-07L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-930-07L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 255.0 lumens
Efficiency: N/A
Efficacy: 31.1 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.49
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865958

CATALOG NUMBER: PRLX-2001-M-930-07L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot



TEST NUMBER: P865958

CATALOG NUMBER: PRLX-2001-M-930-07L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	99	90	83	77	96	88	82	76	85	79	75	81	77	73	78	75	71	69
3	90	79	70	64	87	77	69	63	74	68	62	71	66	61	69	64	60	58
4	82	69	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	55	46	40	67	54	46	40	53	45	39	51	44	39	49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	27	39	32	27	38	32	27	25
10	52	38	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	681
5°	681
10°	684
15°	686
20°	686
25°	691
30°	698
35°	712
40°	732
45°	755
50°	760
55°	750
60°	720
65°	679
70°	620
75°	534
80°	430
85°	292

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 47.5°
 Luminance: 760 cd/sqm

TEST NUMBER: P865958

CATALOG NUMBER: PRLX-2001-M-930-07L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.6	3.0
10°-20°	22.1	8.6
20°-30°	34.1	13.4
30°-40°	43.1	16.9
40°-50°	48.3	18.9
50°-60°	45.1	17.7
60°-70°	33.4	13.1
70°-80°	17.5	6.9
80°-90°	3.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	63.8	25.0
0°-40°	106.9	41.9
0°-60°	200.3	78.6
0°-90°	255.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	255.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	80	
5°	80	8
15°	78	22
25°	74	34
35°	69	43
45°	63	48
55°	51	45
65°	34	33
75°	16	18
85°	3	4
90°	0	

TEST NUMBER: P865958

CATALOG NUMBER: PRLX-2001-M-930-07L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	80.2
2.5°	80.2
5°	80.0
7.5°	79.8
10°	79.4
12.5°	78.9
15°	78.1
17.5°	77.2
20°	76.0
22.5°	75.1
25°	73.8
27.5°	72.7
30°	71.2
32.5°	70.0
35°	68.7
37.5°	67.6
40°	66.1
42.5°	64.6
45°	62.9
47.5°	60.5
50°	57.6
52.5°	54.3
55°	50.7
57.5°	46.8
60°	42.4
62.5°	38.1
65°	33.8
67.5°	29.3
70°	25.0
72.5°	20.7
75°	16.3
77.5°	12.6
80°	8.8
82.5°	5.6
85°	3.0
87.5°	0.9
90°	0.0



TEST NUMBER: P865958
 CATALOG NUMBER: PRLX-2001-M-930-07L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.44	13.11	11.80	13.42	13.74	11.44	13.11	11.80	13.42	13.74
	3H	13.10	14.61	13.47	14.93	15.29	13.10	14.61	13.47	14.93	15.29
	4H	13.66	15.08	14.05	15.43	15.80	13.66	15.08	14.05	15.43	15.80
	6H	14.02	15.34	14.43	15.70	16.09	14.02	15.34	14.43	15.70	16.09
	8H	14.11	15.37	14.53	15.76	16.15	14.11	15.37	14.53	15.76	16.15
	12H	14.15	15.36	14.58	15.74	16.17	14.15	15.36	14.58	15.74	16.17
4H	2H	12.04	13.47	12.44	13.81	14.19	12.04	13.47	12.44	13.81	14.19
	3H	13.91	15.11	14.32	15.50	15.90	13.91	15.11	14.32	15.50	15.90
	4H	14.58	15.66	15.01	16.07	16.51	14.58	15.66	15.01	16.07	16.51
	6H	15.05	15.99	15.50	16.43	16.88	15.05	15.99	15.50	16.43	16.88
	8H	15.17	16.05	15.63	16.49	16.96	15.17	16.05	15.63	16.49	16.96
	12H	15.24	16.03	15.72	16.51	16.98	15.24	16.03	15.72	16.51	16.98
8H	4H	14.84	15.72	15.30	16.16	16.63	14.84	15.72	15.30	16.16	16.63
	6H	15.40	16.13	15.89	16.62	17.09	15.40	16.13	15.89	16.62	17.09
	8H	15.56	16.22	16.07	16.73	17.21	15.56	16.22	16.07	16.73	17.21
	12H	15.68	16.26	16.18	16.75	17.31	15.68	16.26	16.18	16.75	17.31
12H	4H	14.86	15.65	15.34	16.13	16.60	14.86	15.65	15.34	16.13	16.60
	6H	15.42	16.08	15.93	16.59	17.07	15.42	16.08	15.93	16.59	17.07
	8H	15.64	16.22	16.14	16.71	17.27	15.64	16.22	16.14	16.71	17.27