

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865992

Luminaire Tested: PRLX-2001-M-930-45L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-49)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-930-45L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3305.7 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 38.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865992

CATALOG NUMBER: PRLX-2001-M-930-45L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865992

CATALOG NUMBER: PRLX-2001-M-930-45L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98		98	97	95		95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	86		90	86	84		87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75		82	77	74		79	76	73	71
4	90	80	73	67	88	79	72	67	76	71	66		74	69	65		72	68	64	63
5	83	73	65	60	82	72	65	59	70	63	59		68	62	58		66	61	58	56
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61	55	52	50
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42		52	47	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14747
5°	14692
10°	14501
15°	14237
20°	13921
25°	13582
30°	13205
35°	12771
40°	12291
45°	11749
50°	11045
55°	7791
60°	2458
65°	169
70°	119
75°	118
80°	117
85°	117

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11749 cd/sqm

TEST NUMBER: P865992

CATALOG NUMBER: PRLX-2001-M-930-45L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	4.9
10°-20°	456.5	13.8
20°-30°	667.7	20.2
30°-40°	770.7	23.3
40°-50°	754.1	22.8
50°-60°	452.4	13.7
60°-70°	35.3	1.1
70°-80°	4.1	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1287.5	38.9
0°-40°	2058.2	62.3
0°-60°	3264.7	98.8
0°-90°	3305.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3305.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1738	
5°	1725	163
15°	1620	457
25°	1451	668
35°	1233	771
45°	979	754
55°	527	452
65°	8	35
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P865992

CATALOG NUMBER: PRLX-2001-M-930-45L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1737.8
2.5°	1735.4
5°	1724.7
7.5°	1706.7
10°	1682.8
12.5°	1655.2
15°	1620.5
17.5°	1583.4
20°	1541.5
22.5°	1497.3
25°	1450.6
27.5°	1400.3
30°	1347.6
32.5°	1291.4
35°	1232.8
37.5°	1172.9
40°	1109.5
42.5°	1048.4
45°	979.0
47.5°	909.6
50°	836.6
52.5°	718.1
55°	526.6
57.5°	310.0
60°	144.8
62.5°	57.4
65°	8.4
67.5°	4.8
70°	4.8
72.5°	4.8
75°	3.6
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0



TEST NUMBER: P865992
 CATALOG NUMBER: PRLX-2001-M-930-45L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.81	17.19	16.18	17.50	17.82	15.81	17.19	16.18	17.50	17.82
	3H	15.69	16.90	16.07	17.23	17.59	15.69	16.90	16.07	17.23	17.59
	4H	15.63	16.74	16.03	17.09	17.48	15.63	16.74	16.03	17.09	17.48
	6H	15.55	16.58	15.97	16.95	17.34	15.55	16.58	15.97	16.95	17.34
	8H	15.51	16.48	15.94	16.87	17.28	15.51	16.48	15.94	16.87	17.28
	12H	15.47	16.40	15.90	16.78	17.21	15.47	16.40	15.90	16.78	17.21
4H	2H	15.63	16.74	16.03	17.09	17.48	15.63	16.74	16.03	17.09	17.48
	3H	15.51	16.40	15.92	16.81	17.21	15.51	16.40	15.92	16.81	17.21
	4H	15.42	16.22	15.86	16.64	17.08	15.42	16.22	15.86	16.64	17.08
	6H	15.34	16.03	15.81	16.47	16.94	15.34	16.03	15.81	16.47	16.94
	8H	15.29	15.93	15.76	16.37	16.85	15.29	15.93	15.76	16.37	16.85
	12H	15.24	15.81	15.73	16.29	16.76	15.24	15.81	15.73	16.29	16.76
8H	4H	15.29	15.92	15.75	16.37	16.84	15.29	15.92	15.75	16.37	16.84
	6H	15.18	15.71	15.68	16.20	16.69	15.18	15.71	15.68	16.20	16.69
	8H	15.11	15.59	15.63	16.11	16.60	15.11	15.59	15.63	16.11	16.60
	12H	15.06	15.49	15.58	15.99	16.56	15.06	15.49	15.58	15.99	16.56
12H	4H	15.24	15.80	15.72	16.29	16.76	15.24	15.80	15.72	16.29	16.76
	6H	15.11	15.59	15.63	16.11	16.60	15.11	15.59	15.63	16.11	16.60
	8H	15.06	15.49	15.57	15.99	16.56	15.06	15.49	15.57	15.99	16.56