

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866014

Luminaire Tested: PRLX-2001-M-930-75L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-930-75L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2708.8 lumens
Efficiency: N/A
Efficacy: 38.9 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.49
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866014

CATALOG NUMBER: PRLX-2001-M-930-75L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866014

CATALOG NUMBER: PRLX-2001-M-930-75L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	99	90	83	77	96	88	82	76	85	79	75	81	77	73	78	75	71	69
3	90	79	70	64	87	77	69	63	74	68	62	71	66	61	69	64	60	58
4	82	69	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	55	46	40	67	54	46	40	53	45	39	51	44	39	49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	27	39	32	27	38	32	27	25
10	52	38	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7228
5°	7239
10°	7271
15°	7290
20°	7296
25°	7340
30°	7408
35°	7563
40°	7779
45°	8019
50°	8085
55°	7969
60°	7651
65°	7211
70°	6582
75°	5689
80°	4584
85°	3106

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 50°
 Luminance: 8085 cd/sqm

TEST NUMBER: P866014

CATALOG NUMBER: PRLX-2001-M-930-75L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	3.0
10°-20°	234.3	8.6
20°-30°	362.2	13.4
30°-40°	458.1	16.9
40°-50°	512.9	18.9
50°-60°	479.4	17.7
60°-70°	354.5	13.1
70°-80°	186.1	6.9
80°-90°	40.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.4	25.0
0°-40°	1135.5	41.9
0°-60°	2127.8	78.6
0°-90°	2708.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2708.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	852	
5°	850	81
15°	830	234
25°	784	362
35°	730	458
45°	668	513
55°	539	479
65°	359	354
75°	174	186
85°	32	40
90°	0	

TEST NUMBER: P866014

CATALOG NUMBER: PRLX-2001-M-930-75L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	851.8
2.5°	851.8
5°	849.8
7.5°	847.8
10°	843.8
12.5°	837.8
15°	829.8
17.5°	819.8
20°	807.9
22.5°	797.9
25°	783.9
27.5°	772.0
30°	756.0
32.5°	744.0
35°	730.1
37.5°	718.1
40°	702.2
42.5°	686.2
45°	668.2
47.5°	642.3
50°	612.4
52.5°	576.5
55°	538.6
57.5°	496.7
60°	450.8
62.5°	404.9
65°	359.1
67.5°	311.2
70°	265.3
72.5°	219.4
75°	173.5
77.5°	133.6
80°	93.8
82.5°	59.8
85°	31.9
87.5°	10.0
90°	0.0



TEST NUMBER: P866014
 CATALOG NUMBER: PRLX-2001-M-930-75L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.64	21.31	20.00	21.63	21.94	19.64	21.31	20.00	21.63	21.94
	3H	21.30	22.81	21.68	23.14	23.50	21.30	22.81	21.68	23.14	23.50
	4H	21.86	23.29	22.26	23.63	24.01	21.86	23.29	22.26	23.63	24.01
	6H	22.22	23.55	22.63	23.91	24.30	22.22	23.55	22.63	23.91	24.30
	8H	22.31	23.57	22.74	23.96	24.36	22.31	23.57	22.74	23.96	24.36
	12H	22.36	23.57	22.79	23.95	24.38	22.36	23.57	22.79	23.95	24.38
4H	2H	20.25	21.67	20.65	22.02	22.40	20.25	21.67	20.65	22.02	22.40
	3H	22.12	23.31	22.53	23.71	24.11	22.12	23.31	22.53	23.71	24.11
	4H	22.79	23.87	23.22	24.28	24.71	22.79	23.87	23.22	24.28	24.71
	6H	23.26	24.20	23.71	24.64	25.09	23.26	24.20	23.71	24.64	25.09
	8H	23.38	24.26	23.84	24.70	25.16	23.38	24.26	23.84	24.70	25.16
	12H	23.45	24.24	23.93	24.72	25.18	23.45	24.24	23.93	24.72	25.18
8H	4H	23.05	23.93	23.51	24.37	24.84	23.05	23.93	23.51	24.37	24.84
	6H	23.61	24.34	24.10	24.82	25.30	23.61	24.34	24.10	24.82	25.30
	8H	23.77	24.43	24.28	24.94	25.42	23.77	24.43	24.28	24.94	25.42
	12H	23.89	24.47	24.40	24.96	25.52	23.89	24.47	24.40	24.96	25.52
12H	4H	23.07	23.86	23.55	24.34	24.80	23.07	23.86	23.55	24.34	24.80
	6H	23.63	24.29	24.14	24.80	25.28	23.63	24.29	24.14	24.80	25.28
	8H	23.85	24.43	24.35	24.92	25.48	23.85	24.43	24.35	24.92	25.48