

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866020

Luminaire Tested: PRLX-2001-M-935-07L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866020  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-37)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-M-935-07L-G-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 206.1 lumens  
Efficiency: N/A  
Efficacy: 25.1 lumens/watt  
Spacing Criteria (0/90/45): 1.49 / 1.49 / 1.63  
Luminous Opening: Circular (Dia: 1.27' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 8.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866020

CATALOG NUMBER: PRLX-2001-M-935-07L-G-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866020

CATALOG NUMBER: PRLX-2001-M-935-07L-G-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	99	95	106	101	97	94	97	94	91	93	91	88	90	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	78	70	63	87	76	69	62	73	67	61	71	65	60	68	63	59	57
4	81	69	59	52	79	67	59	52	65	57	51	62	56	51	60	55	50	48
5	74	61	51	45	72	60	51	44	57	50	44	55	49	43	54	48	43	41
6	68	54	45	38	66	53	45	38	52	44	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	30
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27
9	54	41	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24
10	51	37	29	24	50	37	29	24	36	28	23	35	28	23	34	28	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	476
5°	478
10°	485
15°	493
20°	505
25°	519
30°	539
35°	566
40°	600
45°	635
50°	650
55°	647
60°	625
65°	580
70°	519
75°	439
80°	327
85°	166

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 50°  
 Luminance: 650 cd/sqm

TEST NUMBER: P866020

CATALOG NUMBER: PRLX-2001-M-935-07L-G-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	5.4	2.6
10°-20°	15.9	7.7
20°-30°	25.6	12.4
30°-40°	34.3	16.6
40°-50°	40.5	19.7
50°-60°	38.9	18.8
60°-70°	28.6	13.9
70°-80°	14.3	7.0
80°-90°	2.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	46.9	22.7
0°-40°	81.2	39.4
0°-60°	160.6	77.9
0°-90°	206.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	206.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	56	
5°	56	5
15°	56	16
25°	55	26
35°	55	34
45°	53	41
55°	44	39
65°	29	29
75°	13	14
85°	2	3
90°	0	

TEST NUMBER: P866020

CATALOG NUMBER: PRLX-2001-M-935-07L-G-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	56.1
2.5°	56.1
5°	56.1
7.5°	56.1
10°	56.3
12.5°	56.1
15°	56.1
17.5°	55.9
20°	55.9
22.5°	55.6
25°	55.4
27.5°	55.2
30°	55.0
32.5°	54.8
35°	54.6
37.5°	54.4
40°	54.2
42.5°	53.8
45°	52.9
47.5°	51.3
50°	49.2
52.5°	46.6
55°	43.7
57.5°	40.4
60°	36.8
62.5°	33.0
65°	28.9
67.5°	25.1
70°	20.9
72.5°	17.2
75°	13.4
77.5°	10.0
80°	6.7
82.5°	4.0
85°	1.7
87.5°	0.4
90°	0.0



TEST NUMBER: P866020  
 CATALOG NUMBER: PRLX-2001-M-935-07L-G-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.12	12.82	11.48	13.13	13.45	11.12	12.82	11.48	13.13	13.45
	3H	12.74	14.27	13.11	14.60	14.96	12.74	14.27	13.11	14.60	14.96
	4H	13.25	14.70	13.65	15.05	15.42	13.25	14.70	13.65	15.05	15.42
	6H	13.56	14.90	13.97	15.26	15.65	13.56	14.90	13.97	15.26	15.65
	8H	13.62	14.90	14.04	15.29	15.69	13.62	14.90	14.04	15.29	15.69
	12H	13.63	14.86	14.06	15.25	15.67	13.63	14.86	14.06	15.25	15.67
4H	2H	11.72	13.17	12.12	13.52	13.89	11.72	13.17	12.12	13.52	13.89
	3H	13.53	14.75	13.94	15.14	15.54	13.53	14.75	13.94	15.14	15.54
	4H	14.16	15.25	14.59	15.67	16.10	14.16	15.25	14.59	15.67	16.10
	6H	14.55	15.51	15.01	15.95	16.40	14.55	15.51	15.01	15.95	16.40
	8H	14.64	15.53	15.10	15.98	16.44	14.64	15.53	15.10	15.98	16.44
	12H	14.68	15.48	15.15	15.95	16.42	14.68	15.48	15.15	15.95	16.42
8H	4H	14.40	15.29	14.85	15.73	16.20	14.40	15.29	14.85	15.73	16.20
	6H	14.86	15.61	15.36	16.09	16.57	14.86	15.61	15.36	16.09	16.57
	8H	14.98	15.65	15.49	16.15	16.64	14.98	15.65	15.49	16.15	16.64
	12H	15.05	15.63	15.55	16.12	16.68	15.05	15.63	15.55	16.12	16.68
12H	4H	14.41	15.22	14.89	15.69	16.16	14.41	15.22	14.89	15.69	16.16
	6H	14.88	15.55	15.39	16.05	16.54	14.88	15.55	15.39	16.05	16.54
	8H	15.04	15.63	15.54	16.12	16.67	15.04	15.63	15.54	16.12	16.67