

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866037

Luminaire Tested: PRLX-2001-M-935-25L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-935-25L-G-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 912.2 lumens
Efficiency: N/A
Efficacy: 42.0 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.49
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 21.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866037

CATALOG NUMBER: PRLX-2001-M-935-25L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866037

CATALOG NUMBER: PRLX-2001-M-935-25L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91		94	91	88		90	88	86	84
2	99	90	83	78	96	88	82	77	85	79	75		82	77	73		79	75	72	69
3	90	79	71	64	87	77	70	63	74	68	62		72	66	61		69	64	60	58
4	82	70	61	54	80	68	60	53	66	59	53		63	57	52		61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45		57	50	45		55	49	44	42
6	69	56	46	40	67	55	46	40	53	45	39		51	44	39		49	43	39	37
7	64	50	41	35	62	49	41	35	48	40	35		46	39	34		45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31		42	36	31		41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	28		39	32	27		38	32	27	25
10	52	39	30	25	51	38	30	25	37	30	25		36	29	25		35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2447
5°	2450
10°	2461
15°	2468
20°	2475
25°	2490
30°	2512
35°	2565
40°	2645
45°	2711
50°	2731
55°	2679
60°	2568
65°	2412
70°	2171
75°	1869
80°	1491
85°	925

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 50°
 Luminance: 2731 cd/sqm

TEST NUMBER: P866037

CATALOG NUMBER: PRLX-2001-M-935-25L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.4	3.0
10°-20°	79.4	8.7
20°-30°	122.7	13.5
30°-40°	155.4	17.0
40°-50°	173.8	19.0
50°-60°	161.3	17.7
60°-70°	118.5	13.0
70°-80°	61.1	6.7
80°-90°	12.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.5	25.2
0°-40°	384.9	42.2
0°-60°	720.0	78.9
0°-90°	912.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	912.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	288	
5°	288	27
15°	281	79
25°	266	123
35°	248	155
45°	226	174
55°	181	161
65°	120	118
75°	57	61
85°	10	13
90°	0	

TEST NUMBER: P866037

CATALOG NUMBER: PRLX-2001-M-935-25L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	288.3
2.5°	288.3
5°	287.6
7.5°	287.0
10°	285.6
12.5°	284.2
15°	280.9
17.5°	278.1
20°	274.1
22.5°	270.0
25°	265.9
27.5°	261.2
30°	256.4
32.5°	252.4
35°	247.6
37.5°	243.5
40°	238.8
42.5°	233.4
45°	225.9
47.5°	217.1
50°	206.9
52.5°	194.7
55°	181.1
57.5°	166.2
60°	151.3
62.5°	135.7
65°	120.1
67.5°	103.8
70°	87.5
72.5°	72.6
75°	57.0
77.5°	43.4
80°	30.5
82.5°	19.0
85°	9.5
87.5°	2.7
90°	0.0



TEST NUMBER: P866037
 CATALOG NUMBER: PRLX-2001-M-935-25L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.82	17.49	16.19	17.80	18.12	15.82	17.49	16.19	17.80	18.12
	3H	17.46	18.97	17.84	19.29	19.65	17.46	18.97	17.84	19.29	19.65
	4H	18.01	19.43	18.40	19.77	20.15	18.01	19.43	18.40	19.77	20.15
	6H	18.35	19.67	18.76	20.03	20.42	18.35	19.67	18.76	20.03	20.42
	8H	18.43	19.69	18.86	20.08	20.48	18.43	19.69	18.86	20.08	20.48
	12H	18.47	19.67	18.89	20.05	20.48	18.47	19.67	18.89	20.05	20.48
4H	2H	16.43	17.85	16.83	18.20	18.57	16.43	17.85	16.83	18.20	18.57
	3H	18.27	19.46	18.68	19.85	20.25	18.27	19.46	18.68	19.85	20.25
	4H	18.92	20.00	19.35	20.41	20.84	18.92	20.00	19.35	20.41	20.84
	6H	19.37	20.31	19.82	20.75	21.20	19.37	20.31	19.82	20.75	21.20
	8H	19.48	20.36	19.94	20.80	21.26	19.48	20.36	19.94	20.80	21.26
	12H	19.54	20.33	20.02	20.80	21.27	19.54	20.33	20.02	20.80	21.27
8H	4H	19.17	20.05	19.63	20.49	20.96	19.17	20.05	19.63	20.49	20.96
	6H	19.71	20.43	20.20	20.92	21.40	19.71	20.43	20.20	20.92	21.40
	8H	19.86	20.51	20.37	21.02	21.50	19.86	20.51	20.37	21.02	21.50
	12H	19.96	20.53	20.46	21.02	21.58	19.96	20.53	20.46	21.02	21.58
12H	4H	19.19	19.98	19.67	20.45	20.92	19.19	19.98	19.67	20.45	20.92
	6H	19.73	20.38	20.24	20.89	21.38	19.73	20.38	20.24	20.89	21.38
	8H	19.93	20.50	20.43	20.99	21.55	19.93	20.50	20.43	20.99	21.55