

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866072

Luminaire Tested: PRLX-2001-M-935-65L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-49)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-935-65L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4871.8 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 58.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866072

CATALOG NUMBER: PRLX-2001-M-935-65L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866072

CATALOG NUMBER: PRLX-2001-M-935-65L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98		98	97	95		95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	86		90	86	84		87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75		82	77	74		79	76	73	71
4	90	80	73	67	88	79	72	67	76	71	66		74	69	65		72	68	64	63
5	83	73	65	60	82	72	65	59	70	63	59		68	62	58		66	61	58	56
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61	55	52	50
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42		52	47	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21734
5°	21650
10°	21369
15°	20981
20°	20516
25°	20016
30°	19460
35°	18820
40°	18113
45°	17315
50°	16277
55°	11482
60°	3622
65°	247
70°	176
75°	174
80°	171
85°	175

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17315 cd/sqm



TEST NUMBER: P866072

CATALOG NUMBER: PRLX-2001-M-935-65L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.6	4.9
10°-20°	672.8	13.8
20°-30°	984.0	20.2
30°-40°	1135.7	23.3
40°-50°	1111.4	22.8
50°-60°	666.7	13.7
60°-70°	52.0	1.1
70°-80°	6.1	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1897.4	38.9
0°-40°	3033.2	62.3
0°-60°	4811.3	98.8
0°-90°	4871.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4871.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2561	
5°	2542	241
15°	2388	673
25°	2138	984
35°	1817	1136
45°	1443	1111
55°	776	667
65°	12	52
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P866072

CATALOG NUMBER: PRLX-2001-M-935-65L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2561.1
2.5°	2557.5
5°	2541.6
7.5°	2515.2
10°	2479.9
12.5°	2439.3
15°	2388.2
17.5°	2333.5
20°	2271.8
22.5°	2206.5
25°	2137.7
27.5°	2063.7
30°	1986.0
32.5°	1903.2
35°	1816.7
37.5°	1728.5
40°	1635.1
42.5°	1545.1
45°	1442.8
47.5°	1340.5
50°	1232.9
52.5°	1058.3
55°	776.1
57.5°	456.8
60°	213.4
62.5°	84.7
65°	12.3
67.5°	7.1
70°	7.1
72.5°	7.1
75°	5.3
77.5°	5.3
80°	3.5
82.5°	3.5
85°	1.8
87.5°	1.8
90°	0.0



TEST NUMBER: P866072
 CATALOG NUMBER: PRLX-2001-M-935-65L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.16	18.54	17.53	18.85	19.17	17.16	18.54	17.53	18.85	19.17
	3H	17.04	18.25	17.42	18.58	18.94	17.04	18.25	17.42	18.58	18.94
	4H	16.97	18.09	17.37	18.44	18.82	16.97	18.09	17.37	18.44	18.82
	6H	16.90	17.92	17.31	18.29	18.69	16.90	17.92	17.31	18.29	18.69
	8H	16.86	17.83	17.29	18.22	18.62	16.86	17.83	17.29	18.22	18.62
	12H	16.82	17.74	17.25	18.13	18.56	16.82	17.74	17.25	18.13	18.56
4H	2H	16.97	18.09	17.37	18.44	18.82	16.97	18.09	17.37	18.44	18.82
	3H	16.85	17.75	17.27	18.15	18.56	16.85	17.75	17.27	18.15	18.56
	4H	16.77	17.56	17.20	17.98	18.43	16.77	17.56	17.20	17.98	18.43
	6H	16.69	17.37	17.15	17.82	18.29	16.69	17.37	17.15	17.82	18.29
	8H	16.63	17.27	17.10	17.72	18.19	16.63	17.27	17.10	17.72	18.19
	12H	16.59	17.15	17.07	17.64	18.11	16.59	17.15	17.07	17.64	18.11
8H	4H	16.63	17.27	17.10	17.72	18.19	16.63	17.27	17.10	17.72	18.19
	6H	16.53	17.05	17.03	17.55	18.03	16.53	17.05	17.03	17.55	18.03
	8H	16.46	16.94	16.98	17.45	17.95	16.46	16.94	16.98	17.45	17.95
	12H	16.41	16.84	16.92	17.34	17.91	16.41	16.84	16.92	17.34	17.91
12H	4H	16.58	17.15	17.07	17.63	18.11	16.58	17.15	17.07	17.63	18.11
	6H	16.46	16.94	16.98	17.45	17.94	16.46	16.94	16.98	17.45	17.94
	8H	16.41	16.84	16.92	17.33	17.90	16.41	16.84	16.92	17.33	17.90