

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866077

Luminaire Tested: PRLX-2001-M-935-75L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866077  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-35)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Pentalux  
Catalog Number: PRLX-2001-M-935-75L-G-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2736.6 lumens  
Efficiency: N/A  
Efficacy: 39.3 lumens/watt  
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.49  
Luminous Opening: Circular (Dia: 1.27' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866077

CATALOG NUMBER: PRLX-2001-M-935-75L-G-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866077

CATALOG NUMBER: PRLX-2001-M-935-75L-G-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91		94	91	88		90	88	86	84
2	99	90	83	78	96	88	82	77	85	79	75		82	77	73		79	75	72	69
3	90	79	71	64	87	77	70	63	74	68	62		72	66	61		69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53		63	57	52		61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45		57	50	45		55	49	44	42
6	69	56	46	40	67	55	46	40	53	45	39		51	44	39		49	43	39	37
7	64	50	41	35	62	49	41	35	48	40	35		46	39	34		45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31		42	36	31		41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	28		39	32	27		38	32	27	25
10	52	39	30	25	51	38	30	25	37	30	25		36	29	25		35	29	25	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7340
5°	7351
10°	7383
15°	7403
20°	7425
25°	7470
30°	7538
35°	7695
40°	7936
45°	8133
50°	8194
55°	8040
60°	7702
65°	7233
70°	6513
75°	5607
80°	4476
85°	2775

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 50°  
 Luminance: 8194 cd/sqm

TEST NUMBER: P866077

CATALOG NUMBER: PRLX-2001-M-935-75L-G-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.2	3.0
10°-20°	238.3	8.7
20°-30°	368.1	13.5
30°-40°	466.3	17.0
40°-50°	521.3	19.0
50°-60°	483.8	17.7
60°-70°	355.3	13.0
70°-80°	183.4	6.7
80°-90°	37.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.5	25.2
0°-40°	1154.8	42.2
0°-60°	2159.9	78.9
0°-90°	2736.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2736.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	865	
5°	863	82
15°	843	238
25°	798	368
35°	743	466
45°	678	521
55°	543	484
65°	360	355
75°	171	183
85°	28	38
90°	0	

TEST NUMBER: P866077

CATALOG NUMBER: PRLX-2001-M-935-75L-G-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	864.9
2.5°	864.9
5°	862.9
7.5°	860.9
10°	856.8
12.5°	852.7
15°	842.6
17.5°	834.4
20°	822.2
22.5°	810.0
25°	797.8
27.5°	783.5
30°	769.3
32.5°	757.1
35°	742.8
37.5°	730.6
40°	716.4
42.5°	700.1
45°	677.7
47.5°	651.3
50°	620.7
52.5°	584.1
55°	543.4
57.5°	498.6
60°	453.8
62.5°	407.0
65°	360.2
67.5°	311.4
70°	262.5
72.5°	217.8
75°	171.0
77.5°	130.3
80°	91.6
82.5°	57.0
85°	28.5
87.5°	8.1
90°	0.0

TEST NUMBER: P866077

CATALOG NUMBER: PRLX-2001-M-935-75L-G-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.64	21.31	20.00	21.62	21.93	19.64	21.31	20.00	21.62	21.93
	3H	21.28	22.79	21.65	23.11	23.47	21.28	22.79	21.65	23.11	23.47
	4H	21.82	23.24	22.22	23.59	23.97	21.82	23.24	22.22	23.59	23.97
	6H	22.17	23.48	22.58	23.85	24.24	22.17	23.48	22.58	23.85	24.24
	8H	22.25	23.51	22.67	23.89	24.29	22.25	23.51	22.67	23.89	24.29
	12H	22.28	23.49	22.71	23.87	24.30	22.28	23.49	22.71	23.87	24.30
4H	2H	20.25	21.67	20.64	22.01	22.39	20.25	21.67	20.64	22.01	22.39
	3H	22.09	23.27	22.50	23.67	24.07	22.09	23.27	22.50	23.67	24.07
	4H	22.74	23.81	23.17	24.23	24.66	22.74	23.81	23.17	24.23	24.66
	6H	23.19	24.12	23.64	24.56	25.02	23.19	24.12	23.64	24.56	25.02
	8H	23.30	24.18	23.76	24.62	25.08	23.30	24.18	23.76	24.62	25.08
	12H	23.36	24.15	23.84	24.62	25.09	23.36	24.15	23.84	24.62	25.09
8H	4H	22.99	23.87	23.45	24.31	24.77	22.99	23.87	23.45	24.31	24.77
	6H	23.52	24.25	24.02	24.74	25.21	23.52	24.25	24.02	24.74	25.21
	8H	23.68	24.33	24.19	24.84	25.32	23.68	24.33	24.19	24.84	25.32
	12H	23.78	24.35	24.28	24.84	25.40	23.78	24.35	24.28	24.84	25.40
12H	4H	23.01	23.80	23.49	24.27	24.74	23.01	23.80	23.49	24.27	24.74
	6H	23.55	24.20	24.06	24.71	25.19	23.55	24.20	24.06	24.71	25.19
	8H	23.75	24.32	24.25	24.81	25.37	23.75	24.32	24.25	24.81	25.37