

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866096

Luminaire Tested: PRLX-2001-M-940-15L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-49)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-940-15L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1189.9 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866096

CATALOG NUMBER: PRLX-2001-M-940-15L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866096

CATALOG NUMBER: PRLX-2001-M-940-15L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	86	90	86	84	87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42	52	47	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5308
5°	5288
10°	5219
15°	5125
20°	5011
25°	4889
30°	4753
35°	4597
40°	4424
45°	4229
50°	3975
55°	2805
60°	884
65°	60
70°	42
75°	43
80°	44
85°	39

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4229 cd/sqm

TEST NUMBER: P866096

CATALOG NUMBER: PRLX-2001-M-940-15L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.8	4.9
10°-20°	164.3	13.8
20°-30°	240.3	20.2
30°-40°	277.4	23.3
40°-50°	271.5	22.8
50°-60°	162.9	13.7
60°-70°	12.7	1.1
70°-80°	1.5	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	463.4	38.9
0°-40°	740.8	62.3
0°-60°	1175.1	98.8
0°-90°	1189.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1189.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	626	
5°	621	59
15°	583	164
25°	522	240
35°	444	277
45°	352	271
55°	190	163
65°	3	13
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P866096

CATALOG NUMBER: PRLX-2001-M-940-15L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	625.5
2.5°	624.7
5°	620.8
7.5°	614.3
10°	605.7
12.5°	595.8
15°	583.3
17.5°	570.0
20°	554.9
22.5°	538.9
25°	522.1
27.5°	504.0
30°	485.1
32.5°	464.8
35°	443.7
37.5°	422.2
40°	399.4
42.5°	377.4
45°	352.4
47.5°	327.4
50°	301.1
52.5°	258.5
55°	189.6
57.5°	111.6
60°	52.1
62.5°	20.7
65°	3.0
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.3
77.5°	1.3
80°	0.9
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

TEST NUMBER: P866096

CATALOG NUMBER: PRLX-2001-M-940-15L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.27	13.64	12.63	13.95	14.27	12.27	13.64	12.63	13.95	14.27
	3H	12.14	13.35	12.52	13.68	14.04	12.14	13.35	12.52	13.68	14.04
	4H	12.08	13.19	12.48	13.54	13.93	12.08	13.19	12.48	13.54	13.93
	6H	12.00	13.03	12.42	13.40	13.79	12.00	13.03	12.42	13.40	13.79
	8H	11.96	12.93	12.39	13.32	13.73	11.96	12.93	12.39	13.32	13.73
	12H	11.92	12.85	12.35	13.23	13.66	11.92	12.85	12.35	13.23	13.66
4H	2H	12.08	13.19	12.48	13.54	13.93	12.08	13.19	12.48	13.54	13.93
	3H	11.96	12.85	12.37	13.26	13.66	11.96	12.85	12.37	13.26	13.66
	4H	11.87	12.67	12.31	13.09	13.53	11.87	12.67	12.31	13.09	13.53
	6H	11.80	12.48	12.26	12.93	13.39	11.80	12.48	12.26	12.93	13.39
	8H	11.74	12.38	12.21	12.83	13.30	11.74	12.38	12.21	12.83	13.30
	12H	11.69	12.26	12.18	12.74	13.22	11.69	12.26	12.18	12.74	13.22
8H	4H	11.74	12.38	12.21	12.82	13.29	11.74	12.38	12.21	12.82	13.29
	6H	11.63	12.16	12.13	12.66	13.14	11.63	12.16	12.13	12.66	13.14
	8H	11.56	12.04	12.09	12.56	13.05	11.56	12.04	12.09	12.56	13.05
	12H	11.51	11.95	12.03	12.44	13.01	11.51	11.95	12.03	12.44	13.01
12H	4H	11.69	12.25	12.17	12.74	13.21	11.69	12.25	12.17	12.74	13.21
	6H	11.56	12.04	12.08	12.56	13.05	11.56	12.04	12.08	12.56	13.05
	8H	11.51	11.95	12.03	12.44	13.01	11.51	11.95	12.03	12.44	13.01