

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866123

Luminaire Tested: PRLX-2001-M-940-45L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-46)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-940-45L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4762.8 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.31
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 38.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866123

CATALOG NUMBER: PRLX-2001-M-940-45L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P866123

CATALOG NUMBER: PRLX-2001-M-940-45L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51
6	75	63	55	49	73	62	54	48	60	53	48	58	52	48	57	52	47	45
7	70	57	49	43	68	56	49	43	55	48	43	54	47	43	52	47	42	41
8	65	52	44	39	64	52	44	39	50	44	39	49	43	38	48	42	38	37
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18765
5°	18683
10°	18476
15°	18189
20°	17869
25°	17522
30°	17160
35°	16776
40°	16350
45°	15821
50°	15049
55°	11397
60°	6120
65°	3944
70°	3977
75°	4194
80°	4359
85°	4401

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15821 cd/sqm

TEST NUMBER: P866123

CATALOG NUMBER: PRLX-2001-M-940-45L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.8	4.4
10°-20°	583.8	12.3
20°-30°	862.4	18.1
30°-40°	1012.6	21.3
40°-50°	1015.1	21.3
50°-60°	679.8	14.3
60°-70°	218.3	4.6
70°-80°	133.5	2.8
80°-90°	49.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1654.0	34.7
0°-40°	2666.6	56.0
0°-60°	4361.5	91.6
0°-90°	4762.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4762.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2211	
5°	2193	208
15°	2070	584
25°	1871	862
35°	1619	1013
45°	1318	1015
55°	770	680
65°	196	218
75°	128	134
85°	45	49
90°	0	

TEST NUMBER: P866123

CATALOG NUMBER: PRLX-2001-M-940-45L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2211.3
2.5°	2207.4
5°	2193.2
7.5°	2172.5
10°	2144.1
12.5°	2111.8
15°	2070.4
17.5°	2027.8
20°	1978.7
22.5°	1928.3
25°	1871.4
27.5°	1814.5
30°	1751.2
32.5°	1686.6
35°	1619.4
37.5°	1549.6
40°	1475.9
42.5°	1401.0
45°	1318.3
47.5°	1234.3
50°	1139.9
52.5°	995.2
55°	770.3
57.5°	546.7
60°	360.6
62.5°	254.6
65°	196.4
67.5°	173.2
70°	160.3
72.5°	144.7
75°	127.9
77.5°	108.6
80°	89.2
82.5°	68.5
85°	45.2
87.5°	23.3
90°	0.0



TEST NUMBER: P866123

CATALOG NUMBER: PRLX-2001-M-940-45L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.47	19.94	18.83	20.26	20.57	18.47	19.94	18.83	20.26	20.57
	3H	18.95	20.26	19.33	20.59	20.95	18.95	20.26	19.33	20.59	20.95
	4H	19.27	20.49	19.67	20.84	21.22	19.27	20.49	19.67	20.84	21.22
	6H	19.60	20.72	20.01	21.09	21.48	19.60	20.72	20.01	21.09	21.48
	8H	19.73	20.81	20.16	21.20	21.60	19.73	20.81	20.16	21.20	21.60
	12H	19.84	20.87	20.27	21.25	21.68	19.84	20.87	20.27	21.25	21.68
4H	2H	18.50	19.73	18.90	20.07	20.45	18.50	19.73	18.90	20.07	20.45
	3H	19.21	20.21	19.62	20.61	21.02	19.21	20.21	19.62	20.61	21.02
	4H	19.68	20.58	20.12	21.00	21.44	19.68	20.58	20.12	21.00	21.44
	6H	20.18	20.96	20.64	21.41	21.87	20.18	20.96	20.64	21.41	21.87
	8H	20.39	21.12	20.86	21.57	22.03	20.39	21.12	20.86	21.57	22.03
	12H	20.56	21.22	21.05	21.70	22.17	20.56	21.22	21.05	21.70	22.17
8H	4H	19.85	20.58	20.31	21.02	21.49	19.85	20.58	20.31	21.02	21.49
	6H	20.48	21.09	20.98	21.58	22.06	20.48	21.09	20.98	21.58	22.06
	8H	20.78	21.33	21.29	21.84	22.33	20.78	21.33	21.29	21.84	22.33
	12H	21.04	21.53	21.55	22.03	22.59	21.04	21.53	21.55	22.03	22.59
12H	4H	19.86	20.51	20.35	20.99	21.47	19.86	20.51	20.35	20.99	21.47
	6H	20.52	21.07	21.04	21.58	22.07	20.52	21.07	21.04	21.58	22.07
	8H	20.88	21.37	21.39	21.87	22.43	20.88	21.37	21.39	21.87	22.43