

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866132

Luminaire Tested: PRLX-2001-M-940-65L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866132  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-37)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-M-940-65L-G-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 7  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2008.6 lumens  
Efficiency: N/A  
Efficacy: 34.3 lumens/watt  
Spacing Criteria (0/90/45): 1.49 / 1.49 / 1.63  
Luminous Opening: Circular (Dia: 1.27' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 58.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866132

CATALOG NUMBER: PRLX-2001-M-940-65L-G-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866132

CATALOG NUMBER: PRLX-2001-M-940-65L-G-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	99	95	106	101	97	94	97	94	91	93	91	88	90	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	78	70	63	87	76	69	62	73	67	61	71	65	60	68	63	59	57
4	81	69	59	52	79	67	59	52	65	57	51	62	56	51	60	55	50	48
5	74	61	51	45	72	60	51	44	57	50	44	55	49	43	54	48	43	41
6	68	54	45	38	66	53	45	38	52	44	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	30
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27
9	54	41	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24
10	51	37	29	24	50	37	29	24	36	28	23	35	28	23	34	28	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4642
5°	4660
10°	4729
15°	4806
20°	4923
25°	5051
30°	5250
35°	5511
40°	5852
45°	6183
50°	6334
55°	6297
60°	6083
65°	5660
70°	5049
75°	4285
80°	3191
85°	1636

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 50°  
 Luminance: 6334 cd/sqm

TEST NUMBER: P866132

CATALOG NUMBER: PRLX-2001-M-940-65L-G-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.3	2.6
10°-20°	154.9	7.7
20°-30°	249.7	12.4
30°-40°	334.1	16.6
40°-50°	395.3	19.7
50°-60°	378.5	18.8
60°-70°	279.1	13.9
70°-80°	139.7	7.0
80°-90°	25.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.8	22.7
0°-40°	791.0	39.4
0°-60°	1564.7	77.9
0°-90°	2008.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2008.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	547	
5°	547	52
15°	547	155
25°	540	250
35°	532	334
45°	515	395
55°	426	379
65°	282	279
75°	131	140
85°	17	25
90°	0	

TEST NUMBER: P866132

CATALOG NUMBER: PRLX-2001-M-940-65L-G-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	547.0
2.5°	547.0
5°	547.0
7.5°	547.0
10°	548.8
12.5°	547.0
15°	547.0
17.5°	545.1
20°	545.1
22.5°	541.4
25°	539.5
27.5°	537.6
30°	535.8
32.5°	533.9
35°	532.0
37.5°	530.2
40°	528.3
42.5°	524.6
45°	515.2
47.5°	500.3
50°	479.8
52.5°	453.6
55°	425.6
57.5°	393.9
60°	358.4
62.5°	321.1
65°	281.9
67.5°	244.6
70°	203.5
72.5°	168.0
75°	130.7
77.5°	97.1
80°	65.3
82.5°	39.2
85°	16.8
87.5°	3.7
90°	0.0



TEST NUMBER: P866132  
 CATALOG NUMBER: PRLX-2001-M-940-65L-G-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.03	20.73	19.40	21.05	21.36	19.03	20.73	19.40	21.05	21.36
	3H	20.65	22.18	21.02	22.51	22.87	20.65	22.18	21.02	22.51	22.87
	4H	21.17	22.62	21.56	22.96	23.34	21.17	22.62	21.56	22.96	23.34
	6H	21.47	22.81	21.88	23.18	23.57	21.47	22.81	21.88	23.18	23.57
	8H	21.53	22.81	21.95	23.20	23.60	21.53	22.81	21.95	23.20	23.60
	12H	21.55	22.78	21.97	23.16	23.59	21.55	22.78	21.97	23.16	23.59
4H	2H	19.63	21.08	20.03	21.43	21.80	19.63	21.08	20.03	21.43	21.80
	3H	21.44	22.66	21.85	23.05	23.45	21.44	22.66	21.85	23.05	23.45
	4H	22.07	23.17	22.50	23.58	24.01	22.07	23.17	22.50	23.58	24.01
	6H	22.47	23.42	22.92	23.86	24.32	22.47	23.42	22.92	23.86	24.32
	8H	22.55	23.45	23.01	23.89	24.35	22.55	23.45	23.01	23.89	24.35
	12H	22.59	23.39	23.07	23.87	24.34	22.59	23.39	23.07	23.87	24.34
8H	4H	22.31	23.20	22.77	23.65	24.11	22.31	23.20	22.77	23.65	24.11
	6H	22.78	23.52	23.27	24.00	24.48	22.78	23.52	23.27	24.00	24.48
	8H	22.90	23.56	23.40	24.07	24.55	22.90	23.56	23.40	24.07	24.55
	12H	22.96	23.55	23.46	24.04	24.60	22.96	23.55	23.46	24.04	24.60
12H	4H	22.32	23.13	22.80	23.60	24.07	22.32	23.13	22.80	23.60	24.07
	6H	22.79	23.46	23.30	23.96	24.45	22.79	23.46	23.30	23.96	24.45
	8H	22.95	23.54	23.46	24.03	24.59	22.95	23.54	23.46	24.03	24.59