

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865437

Luminaire Tested: PRLX-2001-S-927-20L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865437  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-927-20L-G-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 4  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 644.0 lumens  
Efficiency: N/A  
Efficacy: 29.5 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.55  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865437

CATALOG NUMBER: PRLX-2001-S-927-20L-G-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865437

CATALOG NUMBER: PRLX-2001-S-927-20L-G-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	107	102	97	93	105	100	95	91	95	92	89		91	89	86		88	85	83	81
2	97	88	80	74	94	86	79	73	82	76	71		79	74	70		76	72	68	66
3	88	76	67	60	85	75	66	60	72	64	59		69	63	58		66	61	57	54
4	80	67	57	50	77	66	57	50	63	55	49		61	54	48		58	53	48	45
5	73	59	50	43	71	58	49	42	56	48	42		54	47	41		52	46	41	39
6	67	53	44	37	65	52	43	37	50	42	36		48	41	36		47	41	36	33
7	62	48	39	32	60	47	38	32	45	38	32		44	37	31		43	36	31	29
8	58	43	35	28	56	43	34	28	41	34	28		40	33	28		39	32	28	26
9	54	40	31	25	52	39	31	25	38	30	25		37	30	25		36	29	25	23
10	50	37	28	23	49	36	28	23	35	28	23		34	27	23		33	27	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2918
5°	2924
10°	2945
15°	2960
20°	2980
25°	3013
30°	3070
35°	3150
40°	3272
45°	3430
50°	3578
55°	3645
60°	3647
65°	3605
70°	3538
75°	3453
80°	3428
85°	3743

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 87.5°  
 Luminance: 4786 cd/sqm

TEST NUMBER: P865437

CATALOG NUMBER: PRLX-2001-S-927-20L-G-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	17.0	2.6
10°-20°	49.6	7.7
20°-30°	77.4	12.0
30°-40°	99.3	15.4
40°-50°	114.7	17.8
50°-60°	114.2	17.7
60°-70°	92.2	14.3
70°-80°	58.1	9.0
80°-90°	21.5	3.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.9	22.4
0°-40°	243.2	37.8
0°-60°	472.1	73.3
0°-90°	644.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	644.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	179	
5°	179	17
15°	175	50
25°	167	77
35°	158	99
45°	149	115
55°	128	114
65°	93	92
75°	55	58
85°	20	21
90°	0	

TEST NUMBER: P865437

CATALOG NUMBER: PRLX-2001-S-927-20L-G-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	178.9
2.5°	178.9
5°	178.6
7.5°	178.5
10°	177.8
12.5°	176.7
15°	175.3
17.5°	173.7
20°	171.7
22.5°	169.8
25°	167.4
27.5°	165.0
30°	163.0
32.5°	160.6
35°	158.2
37.5°	155.8
40°	153.7
42.5°	151.4
45°	148.7
47.5°	145.5
50°	141.0
52.5°	135.6
55°	128.2
57.5°	120.3
60°	111.8
62.5°	102.7
65°	93.4
67.5°	83.5
70°	74.2
72.5°	64.6
75°	54.8
77.5°	45.6
80°	36.5
82.5°	27.8
85°	20.0
87.5°	12.8
90°	0.0

TEST NUMBER: P865437

CATALOG NUMBER: PRLX-2001-S-927-20L-G-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.98	18.71	17.34	19.03	19.34	16.98	18.71	17.34	19.03	19.34
	3H	18.99	20.57	19.36	20.89	21.25	18.99	20.57	19.36	20.89	21.25
	4H	19.80	21.29	20.20	21.64	22.01	19.80	21.29	20.20	21.64	22.01
	6H	20.47	21.86	20.88	22.22	22.61	20.47	21.86	20.88	22.22	22.61
	8H	20.73	22.06	21.15	22.45	22.85	20.73	22.06	21.15	22.45	22.85
	12H	20.96	22.23	21.38	22.62	23.04	20.96	22.23	21.38	22.62	23.04
4H	2H	17.68	19.18	18.08	19.52	19.90	17.68	19.18	18.08	19.52	19.90
	3H	19.93	21.19	20.33	21.59	21.98	19.93	21.19	20.33	21.59	21.98
	4H	20.88	22.03	21.31	22.44	22.87	20.88	22.03	21.31	22.44	22.87
	6H	21.70	22.71	22.15	23.15	23.60	21.70	22.71	22.15	23.15	23.60
	8H	22.03	22.98	22.48	23.42	23.88	22.03	22.98	22.48	23.42	23.88
	12H	22.32	23.18	22.80	23.66	24.12	22.32	23.18	22.80	23.66	24.12
8H	4H	21.27	22.22	21.73	22.66	23.13	21.27	22.22	21.73	22.66	23.13
	6H	22.25	23.05	22.74	23.53	24.01	22.25	23.05	22.74	23.53	24.01
	8H	22.68	23.40	23.18	23.90	24.38	22.68	23.40	23.18	23.90	24.38
	12H	23.10	23.73	23.60	24.22	24.78	23.10	23.73	23.60	24.22	24.78
12H	4H	21.34	22.20	21.81	22.67	23.13	21.34	22.20	21.81	22.67	23.13
	6H	22.35	23.07	22.85	23.57	24.05	22.35	23.07	22.85	23.57	24.05
	8H	22.86	23.50	23.36	23.98	24.54	22.86	23.50	23.36	23.98	24.54