

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865451

Luminaire Tested: PRLX-2001-S-927-25L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-927-25L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2209.4 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.31
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865451

CATALOG NUMBER: PRLX-2001-S-927-25L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865451

CATALOG NUMBER: PRLX-2001-S-927-25L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	61	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	38	33	32
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15747
5°	15742
10°	15593
15°	15425
20°	15161
25°	14858
30°	14569
35°	14208
40°	13833
45°	13464
50°	13035
55°	12108
60°	9323
65°	4936
70°	2861
75°	2899
80°	3193
85°	3743

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13464 cd/sqm

TEST NUMBER: P865451

CATALOG NUMBER: PRLX-2001-S-927-25L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	4.1
10°-20°	257.1	11.6
20°-30°	380.5	17.2
30°-40°	446.4	20.2
40°-50°	450.2	20.4
50°-60°	371.5	16.8
60°-70°	143.1	6.5
70°-80°	48.8	2.2
80°-90°	20.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.8	33.0
0°-40°	1175.2	53.2
0°-60°	1997.0	90.4
0°-90°	2209.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2209.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	966	
5°	962	91
15°	914	257
25°	826	381
35°	714	446
45°	584	450
55°	426	372
65°	128	143
75°	46	49
85°	20	20
90°	0	

TEST NUMBER: P865451

CATALOG NUMBER: PRLX-2001-S-927-25L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	965.5
2.5°	965.5
5°	961.5
7.5°	953.5
10°	941.5
12.5°	927.5
15°	913.5
17.5°	893.5
20°	873.5
22.5°	851.5
25°	825.6
27.5°	799.6
30°	773.6
32.5°	745.6
35°	713.6
37.5°	681.6
40°	649.7
42.5°	617.7
45°	583.7
47.5°	549.7
50°	513.7
52.5°	473.7
55°	425.8
57.5°	365.8
60°	285.8
62.5°	199.9
65°	127.9
67.5°	82.0
70°	60.0
72.5°	52.0
75°	46.0
77.5°	40.0
80°	34.0
82.5°	28.0
85°	20.0
87.5°	10.0
90°	0.0



TEST NUMBER: P865451
 CATALOG NUMBER: PRLX-2001-S-927-25L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.63	22.14	21.00	22.46	22.77	20.63	22.14	21.00	22.46	22.77
	3H	20.77	22.12	21.15	22.45	22.81	20.77	22.12	21.15	22.45	22.81
	4H	20.83	22.09	21.23	22.44	22.82	20.83	22.09	21.23	22.44	22.82
	6H	20.92	22.07	21.33	22.44	22.83	20.92	22.07	21.33	22.44	22.83
	8H	20.96	22.06	21.39	22.45	22.85	20.96	22.06	21.39	22.45	22.85
	12H	21.00	22.05	21.43	22.44	22.87	21.00	22.05	21.43	22.44	22.87
4H	2H	20.67	21.93	21.07	22.27	22.65	20.67	21.93	21.07	22.27	22.65
	3H	20.89	21.92	21.30	22.32	22.72	20.89	21.92	21.30	22.32	22.72
	4H	21.00	21.92	21.44	22.34	22.78	21.00	21.92	21.44	22.34	22.78
	6H	21.17	21.97	21.63	22.41	22.88	21.17	21.97	21.63	22.41	22.88
	8H	21.26	22.00	21.72	22.45	22.92	21.26	22.00	21.72	22.45	22.92
	12H	21.35	22.01	21.83	22.49	22.96	21.35	22.01	21.83	22.49	22.96
8H	4H	21.00	21.75	21.46	22.19	22.66	21.00	21.75	21.46	22.19	22.66
	6H	21.23	21.85	21.73	22.34	22.82	21.23	21.85	21.73	22.34	22.82
	8H	21.37	21.93	21.89	22.44	22.93	21.37	21.93	21.89	22.44	22.93
	12H	21.54	22.03	22.05	22.53	23.09	21.54	22.03	22.05	22.53	23.09
12H	4H	20.99	21.65	21.47	22.13	22.60	20.99	21.65	21.47	22.13	22.60
	6H	21.23	21.79	21.75	22.30	22.79	21.23	21.79	21.75	22.30	22.79
	8H	21.42	21.92	21.93	22.41	22.97	21.42	21.92	21.93	22.41	22.97