

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865460

Luminaire Tested: PRLX-2001-S-930-10L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-930-10L-G-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 290.3 lumens
Efficiency: N/A
Efficacy: 27.7 lumens/watt
Spacing Criteria (0/90/45): 1.52 / 1.52 / 1.69
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865460

CATALOG NUMBER: PRLX-2001-S-930-10L-G-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865460

CATALOG NUMBER: PRLX-2001-S-930-10L-G-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	107	102	97	92	104	99	95	91	95	91	88		91	88	85		87	85	82	80
2	96	87	79	73	93	85	78	72	81	75	70		78	73	68		75	71	67	64
3	87	75	66	59	84	73	65	58	70	63	57		67	61	56		65	60	55	53
4	79	66	56	49	76	64	55	48	62	54	47		59	52	47		57	51	46	44
5	72	58	48	41	70	57	48	41	55	46	40		53	45	40		51	44	39	37
6	66	52	42	35	64	51	42	35	49	41	35		47	40	34		45	39	34	32
7	61	46	37	30	59	46	37	30	44	36	30		43	35	30		41	35	30	27
8	57	42	33	27	55	41	33	27	40	32	27		39	32	26		37	31	26	24
9	53	38	30	24	51	38	29	24	37	29	24		35	28	23		34	28	23	21
10	49	35	27	21	48	35	27	21	34	26	21		33	26	21		32	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1127
5°	1135
10°	1156
15°	1180
20°	1210
25°	1247
30°	1299
35°	1364
40°	1448
45°	1557
50°	1662
55°	1718
60°	1735
65°	1729
70°	1712
75°	1676
80°	1662
85°	1853

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 87.5°
 Luminance: 2393 cd/sqm

TEST NUMBER: P865460

CATALOG NUMBER: PRLX-2001-S-930-10L-G-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.6	2.3
10°-20°	19.8	6.8
20°-30°	32.1	11.1
30°-40°	43.0	14.8
40°-50°	52.0	17.9
50°-60°	53.7	18.5
60°-70°	44.3	15.2
70°-80°	28.2	9.7
80°-90°	10.6	3.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	58.5	20.2
0°-40°	101.6	35.0
0°-60°	207.3	71.4
0°-90°	290.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	290.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	69	
5°	69	7
15°	70	20
25°	69	32
35°	68	43
45°	68	52
55°	60	54
65°	45	44
75°	27	28
85°	10	11
90°	0	

TEST NUMBER: P865460

CATALOG NUMBER: PRLX-2001-S-930-10L-G-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	69.1
2.5°	69.1
5°	69.3
7.5°	69.7
10°	69.8
12.5°	70.0
15°	69.9
17.5°	69.8
20°	69.7
22.5°	69.7
25°	69.3
27.5°	69.2
30°	69.0
32.5°	68.8
35°	68.5
37.5°	68.3
40°	68.0
42.5°	67.8
45°	67.5
47.5°	66.8
50°	65.5
52.5°	63.3
55°	60.4
57.5°	56.9
60°	53.2
62.5°	49.1
65°	44.8
67.5°	40.4
70°	35.9
72.5°	31.2
75°	26.6
77.5°	22.2
80°	17.7
82.5°	13.7
85°	9.9
87.5°	6.4
90°	0.0



TEST NUMBER: P865460
 CATALOG NUMBER: PRLX-2001-S-930-10L-G-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.50	16.27	14.87	16.59	16.90	14.50	16.27	14.87	16.59	16.90
	3H	16.59	18.20	16.96	18.52	18.88	16.59	18.20	16.96	18.52	18.88
	4H	17.42	18.94	17.81	19.29	19.66	17.42	18.94	17.81	19.29	19.66
	6H	18.11	19.53	18.52	19.89	20.28	18.11	19.53	18.52	19.89	20.28
	8H	18.38	19.75	18.80	20.13	20.53	18.38	19.75	18.80	20.13	20.53
	12H	18.62	19.93	19.05	20.31	20.74	18.62	19.93	19.05	20.31	20.74
4H	2H	15.23	16.76	15.63	17.10	17.48	15.23	16.76	15.63	17.10	17.48
	3H	17.54	18.84	17.95	19.23	19.63	17.54	18.84	17.95	19.23	19.63
	4H	18.52	19.70	18.95	20.11	20.54	18.52	19.70	18.95	20.11	20.54
	6H	19.36	20.40	19.81	20.84	21.29	19.36	20.40	19.81	20.84	21.29
	8H	19.70	20.68	20.16	21.12	21.58	19.70	20.68	20.16	21.12	21.58
	12H	20.01	20.90	20.49	21.37	21.84	20.01	20.90	20.49	21.37	21.84
8H	4H	18.92	19.90	19.38	20.34	20.80	18.92	19.90	19.38	20.34	20.80
	6H	19.93	20.75	20.41	21.23	21.70	19.93	20.75	20.41	21.23	21.70
	8H	20.37	21.11	20.88	21.61	22.10	20.37	21.11	20.88	21.61	22.10
	12H	20.81	21.47	21.31	21.95	22.51	20.81	21.47	21.31	21.95	22.51
12H	4H	18.99	19.88	19.47	20.35	20.82	18.99	19.88	19.47	20.35	20.82
	6H	20.03	20.77	20.53	21.27	21.76	20.03	20.77	20.53	21.27	21.76
	8H	20.56	21.22	21.06	21.70	22.26	20.56	21.22	21.06	21.70	22.26