

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246979

Luminaire Tested: **LD8B90D010 ER8B90935 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246979
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B90D010 ER8B90935 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8262.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246979

CATALOG NUMBER: LD8B90D010 ER8B90935 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P246979

CATALOG NUMBER: LD8B90D010 ER8B90935 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	418085
5°	400654
10°	353287
15°	297734
20°	244458
25°	198136
30°	146682
35°	88294
40°	39320
45°	15289
50°	5483
55°	1602
60°	1122
65°	839
70°	90
75°	453
80°	0
85°	1344



TEST NUMBER: P246979

CATALOG NUMBER: LD8B90D010 ER8B90935 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1181.7	14.3
10°-20°	2590.4	31.4
20°-30°	2641.8	32.0
30°-40°	1479.6	17.9
40°-50°	315.5	3.8
50°-60°	39.1	0.5
60°-70°	10.2	0.1
70°-80°	2.4	0.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6413.9	77.6
0°-40°	7893.5	95.5
0°-60°	8248.1	99.8
0°-90°	8262.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8262.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13558	
5°	12944	###
15°	9326	2590
25°	5823	2642
35°	2346	1480
45°	351	316
55°	30	39
65°	12	10
75°	4	2
85°	4	1
90°	0	



TEST NUMBER: P246979

CATALOG NUMBER: LD8B90D010 ER8B90935 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13558.2
2.5°	13405.5
5°	12943.5
7.5°	12200.1
10°	11282.8
12.5°	10298.3
15°	9326.3
17.5°	8348.5
20°	7449.5
22.5°	6612.9
25°	5823.4
27.5°	4994.5
30°	4119.5
32.5°	3205.1
35°	2345.5
37.5°	1571.4
40°	976.8
42.5°	584.0
45°	350.6
47.5°	195.0
50°	114.3
52.5°	60.5
55°	29.8
57.5°	21.1
60°	18.2
62.5°	8.6
65°	11.5
67.5°	11.5
70°	1.0
72.5°	2.9
75°	3.8
77.5°	1.9
80°	0.0
82.5°	1.0
85°	3.8
87.5°	0.0
90°	0.0

(END OF REPORT)