

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865467

Luminaire Tested: PRLX-2001-S-930-10L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865467  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-930-10L-L-U-S-X-X-WHHR-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 955.1 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.31  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 10.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865467

CATALOG NUMBER: PRLX-2001-S-930-10L-L-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865467

CATALOG NUMBER: PRLX-2001-S-930-10L-L-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	61	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	38	33	32
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6808
5°	6806
10°	6741
15°	6668
20°	6554
25°	6423
30°	6298
35°	6143
40°	5981
45°	5820
50°	5636
55°	5235
60°	4032
65°	2134
70°	1235
75°	1254
80°	1381
85°	1609

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5820 cd/sqm

TEST NUMBER: P865467

CATALOG NUMBER: PRLX-2001-S-930-10L-L-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.4	4.1
10°-20°	111.2	11.6
20°-30°	164.5	17.2
30°-40°	193.0	20.2
40°-50°	194.6	20.4
50°-60°	160.6	16.8
60°-70°	61.9	6.5
70°-80°	21.1	2.2
80°-90°	8.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.1	33.0
0°-40°	508.1	53.2
0°-60°	863.3	90.4
0°-90°	955.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	955.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	417	
5°	416	39
15°	395	111
25°	357	164
35°	308	193
45°	252	195
55°	184	161
65°	55	62
75°	20	21
85°	9	9
90°	0	

TEST NUMBER: P865467

CATALOG NUMBER: PRLX-2001-S-930-10L-L-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	417.4
2.5°	417.4
5°	415.7
7.5°	412.2
10°	407.0
12.5°	401.0
15°	394.9
17.5°	386.3
20°	377.6
22.5°	368.1
25°	356.9
27.5°	345.7
30°	334.4
32.5°	322.3
35°	308.5
37.5°	294.7
40°	280.9
42.5°	267.0
45°	252.3
47.5°	237.6
50°	222.1
52.5°	204.8
55°	184.1
57.5°	158.1
60°	123.6
62.5°	86.4
65°	55.3
67.5°	35.4
70°	25.9
72.5°	22.5
75°	19.9
77.5°	17.3
80°	14.7
82.5°	12.1
85°	8.6
87.5°	4.3
90°	0.0



TEST NUMBER: P865467  
 CATALOG NUMBER: PRLX-2001-S-930-10L-L-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.72	19.23	18.08	19.54	19.86	17.72	19.23	18.08	19.54	19.86
	3H	17.86	19.20	18.23	19.53	19.89	17.86	19.20	18.23	19.53	19.89
	4H	17.92	19.17	18.32	19.52	19.90	17.92	19.17	18.32	19.52	19.90
	6H	18.00	19.16	18.41	19.53	19.92	18.00	19.16	18.41	19.53	19.92
	8H	18.04	19.15	18.47	19.54	19.94	18.04	19.15	18.47	19.54	19.94
	12H	18.09	19.14	18.52	19.52	19.95	18.09	19.14	18.52	19.52	19.95
4H	2H	17.75	19.01	18.15	19.36	19.74	17.75	19.01	18.15	19.36	19.74
	3H	17.97	19.00	18.38	19.40	19.80	17.97	19.00	18.38	19.40	19.80
	4H	18.09	19.01	18.52	19.42	19.86	18.09	19.01	18.52	19.42	19.86
	6H	18.26	19.06	18.72	19.50	19.96	18.26	19.06	18.72	19.50	19.96
	8H	18.34	19.09	18.81	19.53	20.00	18.34	19.09	18.81	19.53	20.00
	12H	18.43	19.10	18.91	19.58	20.05	18.43	19.10	18.91	19.58	20.05
8H	4H	18.08	18.83	18.55	19.28	19.74	18.08	18.83	18.55	19.28	19.74
	6H	18.32	18.94	18.82	19.43	19.91	18.32	18.94	18.82	19.43	19.91
	8H	18.46	19.02	18.97	19.53	20.02	18.46	19.02	18.97	19.53	20.02
	12H	18.62	19.12	19.13	19.61	20.18	18.62	19.12	19.13	19.61	20.18
12H	4H	18.07	18.74	18.55	19.22	19.69	18.07	18.74	18.55	19.22	19.69
	6H	18.32	18.87	18.83	19.38	19.87	18.32	18.87	18.83	19.38	19.87
	8H	18.50	19.00	19.01	19.49	20.06	18.50	19.00	19.01	19.49	20.06