

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865488

Luminaire Tested: PRLX-2001-S-930-25L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-930-25L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1926.2 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.29
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865488

CATALOG NUMBER: PRLX-2001-S-930-25L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865488

CATALOG NUMBER: PRLX-2001-S-930-25L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	88	78	70	64	86	77	70	64	74	68	63	72	67	62	70	65	62	60
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	64	59	54	53
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42
8	66	53	45	40	64	52	45	40	51	44	40	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14976
5°	14961
10°	14849
15°	14592
20°	14325
25°	14035
30°	13590
35°	13163
40°	12696
45°	12209
50°	11677
55°	10811
60°	7610
65°	2501
70°	205
75°	139
80°	207
85°	412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12209 cd/sqm

TEST NUMBER: P865488

CATALOG NUMBER: PRLX-2001-S-930-25L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	4.5
10°-20°	243.4	12.6
20°-30°	357.8	18.6
30°-40°	413.1	21.4
40°-50°	408.3	21.2
50°-60°	327.4	17.0
60°-70°	84.8	4.4
70°-80°	2.6	0.1
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.9	35.7
0°-40°	1101.0	57.2
0°-60°	1836.6	95.4
0°-90°	1926.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1926.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	918	
5°	914	87
15°	864	243
25°	780	358
35°	661	413
45°	529	408
55°	380	327
65°	65	85
75°	2	3
85°	2	2
90°	0	

TEST NUMBER: P865488

CATALOG NUMBER: PRLX-2001-S-930-25L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	918.2
2.5°	916.0
5°	913.8
7.5°	907.4
10°	896.6
12.5°	879.3
15°	864.2
17.5°	844.7
20°	825.3
22.5°	801.5
25°	779.9
27.5°	749.7
30°	721.6
32.5°	691.3
35°	661.1
37.5°	628.7
40°	596.3
42.5°	563.9
45°	529.3
47.5°	494.7
50°	460.2
52.5°	423.4
55°	380.2
57.5°	317.6
60°	233.3
62.5°	140.4
65°	64.8
67.5°	23.8
70°	4.3
72.5°	2.2
75°	2.2
77.5°	2.2
80°	2.2
82.5°	2.2
85°	2.2
87.5°	2.2
90°	0.0



TEST NUMBER: P865488
 CATALOG NUMBER: PRLX-2001-S-930-25L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.18	21.63	20.55	21.94	22.26	20.18	21.63	20.55	21.94	22.26
	3H	20.08	21.36	20.46	21.69	22.05	20.08	21.36	20.46	21.69	22.05
	4H	20.01	21.20	20.42	21.55	21.93	20.01	21.20	20.42	21.55	21.93
	6H	19.95	21.04	20.36	21.40	21.80	19.95	21.04	20.36	21.40	21.80
	8H	19.91	20.94	20.34	21.33	21.74	19.91	20.94	20.34	21.33	21.74
	12H	19.87	20.86	20.30	21.24	21.67	19.87	20.86	20.30	21.24	21.67
4H	2H	20.08	21.27	20.49	21.62	22.00	20.08	21.27	20.49	21.62	22.00
	3H	19.99	20.95	20.40	21.35	21.75	19.99	20.95	20.40	21.35	21.75
	4H	19.91	20.76	20.34	21.18	21.62	19.91	20.76	20.34	21.18	21.62
	6H	19.84	20.57	20.30	21.02	21.48	19.84	20.57	20.30	21.02	21.48
	8H	19.79	20.47	20.26	20.92	21.39	19.79	20.47	20.26	20.92	21.39
	12H	19.75	20.36	20.23	20.84	21.31	19.75	20.36	20.23	20.84	21.31
8H	4H	19.79	20.47	20.25	20.92	21.39	19.79	20.47	20.25	20.92	21.39
	6H	19.69	20.26	20.19	20.75	21.23	19.69	20.26	20.19	20.75	21.23
	8H	19.63	20.14	20.15	20.65	21.14	19.63	20.14	20.15	20.65	21.14
	12H	19.59	20.04	20.10	20.54	21.11	19.59	20.04	20.10	20.54	21.11
12H	4H	19.74	20.35	20.23	20.83	21.31	19.74	20.35	20.23	20.83	21.31
	6H	19.63	20.14	20.15	20.65	21.14	19.63	20.14	20.15	20.65	21.14
	8H	19.59	20.04	20.10	20.54	21.10	19.59	20.04	20.10	20.54	21.10