

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865502

Luminaire Tested: PRLX-2001-S-935-10L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-935-10L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 362.6 lumens
Efficiency: N/A
Efficacy: 34.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.55
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865502

CATALOG NUMBER: PRLX-2001-S-935-10L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865502

CATALOG NUMBER: PRLX-2001-S-935-10L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	102	97	93	105	100	95	91	95	92	88	91	88	86	88	85	83	81
2	97	88	80	74	94	86	79	73	82	76	71	79	74	70	76	72	68	66
3	88	76	67	60	85	75	66	60	71	64	59	69	63	58	66	61	56	54
4	80	67	57	50	77	65	57	50	63	55	49	60	54	48	58	52	48	45
5	73	59	50	43	71	58	49	42	56	48	42	54	47	41	52	46	41	39
6	67	53	44	37	65	52	43	37	50	42	36	48	41	36	47	40	35	33
7	62	48	39	32	60	47	38	32	45	37	32	44	37	31	42	36	31	29
8	58	43	34	28	56	43	34	28	41	34	28	40	33	28	39	32	28	26
9	54	40	31	25	52	39	31	25	38	30	25	37	30	25	36	29	25	23
10	50	36	28	23	49	36	28	23	35	28	23	34	27	22	33	27	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1629
5°	1634
10°	1646
15°	1655
20°	1670
25°	1690
30°	1721
35°	1768
40°	1842
45°	1933
50°	2020
55°	2059
60°	2055
65°	2034
70°	1993
75°	1954
80°	1944
85°	2115

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 87.5°
 Luminance: 2730 cd/sqm

TEST NUMBER: P865502

CATALOG NUMBER: PRLX-2001-S-935-10L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.5	2.6
10°-20°	27.7	7.6
20°-30°	43.4	12.0
30°-40°	55.8	15.4
40°-50°	64.6	17.8
50°-60°	64.5	17.8
60°-70°	52.1	14.4
70°-80°	32.9	9.1
80°-90°	12.2	3.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.6	22.2
0°-40°	136.4	37.6
0°-60°	265.5	73.2
0°-90°	362.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	362.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	100	
5°	100	10
15°	98	28
25°	94	43
35°	89	56
45°	84	65
55°	72	64
65°	53	52
75°	31	33
85°	11	12
90°	0	

TEST NUMBER: P865502

CATALOG NUMBER: PRLX-2001-S-935-10L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	99.9
2.5°	99.8
5°	99.8
7.5°	99.7
10°	99.4
12.5°	98.8
15°	98.0
17.5°	97.1
20°	96.2
22.5°	95.0
25°	93.9
27.5°	92.7
30°	91.4
32.5°	90.2
35°	88.8
37.5°	87.8
40°	86.5
42.5°	85.2
45°	83.8
47.5°	82.1
50°	79.6
52.5°	76.5
55°	72.4
57.5°	67.9
60°	63.0
62.5°	57.9
65°	52.7
67.5°	47.3
70°	41.8
72.5°	36.5
75°	31.0
77.5°	25.8
80°	20.7
82.5°	15.8
85°	11.3
87.5°	7.3
90°	0.0



TEST NUMBER: P865502
 CATALOG NUMBER: PRLX-2001-S-935-10L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.00	16.73	15.36	17.05	17.36	15.00	16.73	15.36	17.05	17.36
	3H	17.01	18.59	17.39	18.92	19.28	17.01	18.59	17.39	18.92	19.28
	4H	17.82	19.32	18.22	19.66	20.04	17.82	19.32	18.22	19.66	20.04
	6H	18.50	19.89	18.91	20.25	20.64	18.50	19.89	18.91	20.25	20.64
	8H	18.76	20.09	19.18	20.48	20.88	18.76	20.09	19.18	20.48	20.88
	12H	18.99	20.27	19.42	20.65	21.08	18.99	20.27	19.42	20.65	21.08
4H	2H	15.70	17.20	16.10	17.54	17.92	15.70	17.20	16.10	17.54	17.92
	3H	17.95	19.21	18.35	19.61	20.01	17.95	19.21	18.35	19.61	20.01
	4H	18.90	20.05	19.33	20.46	20.90	18.90	20.05	19.33	20.46	20.90
	6H	19.73	20.74	20.18	21.18	21.63	19.73	20.74	20.18	21.18	21.63
	8H	20.06	21.01	20.52	21.45	21.91	20.06	21.01	20.52	21.45	21.91
	12H	20.36	21.22	20.83	21.69	22.16	20.36	21.22	20.83	21.69	22.16
8H	4H	19.30	20.25	19.75	20.69	21.15	19.30	20.25	19.75	20.69	21.15
	6H	20.28	21.08	20.77	21.57	22.04	20.28	21.08	20.77	21.57	22.04
	8H	20.72	21.44	21.22	21.94	22.42	20.72	21.44	21.22	21.94	22.42
	12H	21.13	21.77	21.63	22.26	22.81	21.13	21.77	21.63	22.26	22.81
12H	4H	19.36	20.22	19.84	20.69	21.16	19.36	20.22	19.84	20.69	21.16
	6H	20.38	21.10	20.89	21.61	22.09	20.38	21.10	20.89	21.61	22.09
	8H	20.89	21.53	21.40	22.02	22.58	20.89	21.53	21.40	22.02	22.58