

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865506

Luminaire Tested: PRLX-2001-S-935-10L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865506  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-935-10L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 847.1 lumens  
Efficiency: N/A  
Efficacy: 80.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.28  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 10.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865506

CATALOG NUMBER: PRLX-2001-S-935-10L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865506

CATALOG NUMBER: PRLX-2001-S-935-10L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	75	63	55	50	74	62	55	49	61	54	49	59	53	49	58	52	48	46
7	70	58	50	44	69	57	49	44	56	49	44	54	48	43	53	47	43	41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6596
5°	6577
10°	6504
15°	6371
20°	6235
25°	6090
30°	5931
35°	5728
40°	5529
45°	5321
50°	5075
55°	4709
60°	3334
65°	1223
70°	300
75°	284
80°	338
85°	337

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5321 cd/sqm

TEST NUMBER: P865506

CATALOG NUMBER: PRLX-2001-S-935-10L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.1	4.5
10°-20°	106.4	12.6
20°-30°	155.9	18.4
30°-40°	180.0	21.2
40°-50°	177.7	21.0
50°-60°	142.7	16.8
60°-70°	39.8	4.7
70°-80°	4.6	0.5
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.3	35.5
0°-40°	480.3	56.7
0°-60°	800.7	94.5
0°-90°	847.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	404	
5°	402	38
15°	377	106
25°	338	156
35°	288	180
45°	231	178
55°	166	143
65°	32	40
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P865506

CATALOG NUMBER: PRLX-2001-S-935-10L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	404.4
2.5°	404.4
5°	401.7
7.5°	398.1
10°	392.7
12.5°	385.4
15°	377.3
17.5°	369.1
20°	359.2
22.5°	349.2
25°	338.4
27.5°	327.5
30°	314.9
32.5°	301.3
35°	287.7
37.5°	274.1
40°	259.7
42.5°	245.2
45°	230.7
47.5°	215.3
50°	200.0
52.5°	184.6
55°	165.6
57.5°	138.4
60°	102.2
62.5°	62.4
65°	31.7
67.5°	14.5
70°	6.3
72.5°	4.5
75°	4.5
77.5°	3.6
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0



TEST NUMBER: P865506  
 CATALOG NUMBER: PRLX-2001-S-935-10L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.25	18.71	17.62	19.03	19.34	17.25	18.71	17.62	19.03	19.34
	3H	17.18	18.47	17.56	18.80	19.16	17.18	18.47	17.56	18.80	19.16
	4H	17.12	18.32	17.52	18.67	19.05	17.12	18.32	17.52	18.67	19.05
	6H	17.06	18.16	17.48	18.53	18.93	17.06	18.16	17.48	18.53	18.93
	8H	17.03	18.08	17.46	18.47	18.87	17.03	18.08	17.46	18.47	18.87
	12H	17.00	18.00	17.43	18.38	18.81	17.00	18.00	17.43	18.38	18.81
4H	2H	17.18	18.37	17.58	18.72	19.10	17.18	18.37	17.58	18.72	19.10
	3H	17.11	18.08	17.52	18.48	18.88	17.11	18.08	17.52	18.48	18.88
	4H	17.05	17.91	17.48	18.33	18.77	17.05	17.91	17.48	18.33	18.77
	6H	17.00	17.74	17.46	18.18	18.65	17.00	17.74	17.46	18.18	18.65
	8H	16.96	17.65	17.42	18.10	18.57	16.96	17.65	17.42	18.10	18.57
	12H	16.92	17.54	17.41	18.02	18.49	16.92	17.54	17.41	18.02	18.49
8H	4H	16.93	17.63	17.40	18.07	18.54	16.93	17.63	17.40	18.07	18.54
	6H	16.86	17.44	17.36	17.93	18.41	16.86	17.44	17.36	17.93	18.41
	8H	16.82	17.34	17.34	17.85	18.34	16.82	17.34	17.34	17.85	18.34
	12H	16.79	17.26	17.31	17.75	18.32	16.79	17.26	17.31	17.75	18.32
12H	4H	16.89	17.51	17.38	17.99	18.46	16.89	17.51	17.38	17.99	18.46
	6H	16.81	17.32	17.33	17.84	18.33	16.81	17.32	17.33	17.84	18.33
	8H	16.78	17.25	17.30	17.74	18.31	16.78	17.25	17.30	17.74	18.31