

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865510

Luminaire Tested: PRLX-2001-S-935-15L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865510  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-935-15L-G-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 3  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 544.0 lumens  
Efficiency: N/A  
Efficacy: 34.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.55  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865510

CATALOG NUMBER: PRLX-2001-S-935-15L-G-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865510

CATALOG NUMBER: PRLX-2001-S-935-15L-G-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	107	102	97	93	105	100	95	91	95	92	88		91	88	86		88	85	83	81
2	97	88	80	74	94	86	79	73	82	76	71		79	74	70		76	72	68	66
3	88	76	67	60	85	75	66	60	71	64	59		69	63	57		66	61	56	54
4	80	67	57	50	77	65	57	50	63	55	49		60	54	48		58	52	48	45
5	73	59	50	43	71	58	49	42	56	48	42		54	47	41		52	46	41	39
6	67	53	43	37	65	52	43	37	50	42	36		48	41	36		47	40	35	33
7	62	48	39	32	60	47	38	32	45	37	32		44	37	31		42	36	31	29
8	58	43	34	28	56	43	34	28	41	34	28		40	33	28		39	32	28	26
9	54	40	31	25	52	39	31	25	38	30	25		37	30	25		36	29	25	23
10	50	36	28	23	49	36	28	23	35	28	23		34	27	22		33	27	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2443
5°	2451
10°	2471
15°	2482
20°	2505
25°	2536
30°	2582
35°	2654
40°	2761
45°	2899
50°	3030
55°	3088
60°	3083
65°	3053
70°	2990
75°	2937
80°	2921
85°	3181

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 87.5°  
 Luminance: 4113 cd/sqm

TEST NUMBER: P865510

CATALOG NUMBER: PRLX-2001-S-935-15L-G-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	14.3	2.6
10°-20°	41.6	7.6
20°-30°	65.1	12.0
30°-40°	83.7	15.4
40°-50°	96.9	17.8
50°-60°	96.7	17.8
60°-70°	78.1	14.4
70°-80°	49.3	9.1
80°-90°	18.3	3.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	120.9	22.2
0°-40°	204.6	37.6
0°-60°	398.2	73.2
0°-90°	544.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	150	
5°	150	14
15°	147	42
25°	141	65
35°	133	84
45°	126	97
55°	109	97
65°	79	78
75°	47	49
85°	17	18
90°	0	

TEST NUMBER: P865510

CATALOG NUMBER: PRLX-2001-S-935-15L-G-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	149.8
2.5°	149.7
5°	149.7
7.5°	149.6
10°	149.2
12.5°	148.2
15°	147.0
17.5°	145.6
20°	144.3
22.5°	142.5
25°	140.9
27.5°	139.1
30°	137.1
32.5°	135.3
35°	133.3
37.5°	131.6
40°	129.7
42.5°	127.8
45°	125.7
47.5°	123.1
50°	119.4
52.5°	114.7
55°	108.6
57.5°	101.8
60°	94.5
62.5°	86.9
65°	79.1
67.5°	71.0
70°	62.7
72.5°	54.7
75°	46.6
77.5°	38.7
80°	31.1
82.5°	23.8
85°	17.0
87.5°	11.0
90°	0.0



TEST NUMBER: P865510  
 CATALOG NUMBER: PRLX-2001-S-935-15L-G-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.40	18.14	16.77	18.45	18.77	16.40	18.14	16.77	18.45	18.77
	3H	18.42	20.00	18.79	20.32	20.68	18.42	20.00	18.79	20.32	20.68
	4H	19.23	20.73	19.63	21.07	21.45	19.23	20.73	19.63	21.07	21.45
	6H	19.91	21.30	20.32	21.66	22.05	19.91	21.30	20.32	21.66	22.05
	8H	20.17	21.51	20.60	21.89	22.29	20.17	21.51	20.60	21.89	22.29
	12H	20.40	21.68	20.83	22.06	22.49	20.40	21.68	20.83	22.06	22.49
4H	2H	17.11	18.60	17.50	18.95	19.32	17.11	18.60	17.50	18.95	19.32
	3H	19.35	20.62	19.76	21.02	21.41	19.35	20.62	19.76	21.02	21.41
	4H	20.31	21.46	20.74	21.88	22.31	20.31	21.46	20.74	21.88	22.31
	6H	21.14	22.15	21.59	22.59	23.04	21.14	22.15	21.59	22.59	23.04
	8H	21.47	22.42	21.93	22.86	23.33	21.47	22.42	21.93	22.86	23.33
	12H	21.77	22.63	22.25	23.10	23.57	21.77	22.63	22.25	23.10	23.57
8H	4H	20.71	21.66	21.16	22.10	22.56	20.71	21.66	21.16	22.10	22.56
	6H	21.69	22.49	22.18	22.98	23.45	21.69	22.49	22.18	22.98	23.45
	8H	22.13	22.85	22.63	23.35	23.83	22.13	22.85	22.63	23.35	23.83
	12H	22.55	23.19	23.05	23.68	24.23	22.55	23.19	23.05	23.68	24.23
12H	4H	20.77	21.63	21.25	22.11	22.57	20.77	21.63	21.25	22.11	22.57
	6H	21.79	22.52	22.30	23.02	23.50	21.79	22.52	22.30	23.02	23.50
	8H	22.31	22.95	22.81	23.44	23.99	22.31	22.95	22.81	23.44	23.99