

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865515

Luminaire Tested: PRLX-2001-S-935-15L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865515  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-935-15L-L-U-S-X-X-WHHR-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS,  
TAPERED DRUM WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 3  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1500.0 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.31  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865515

CATALOG NUMBER: PRLX-2001-S-935-15L-L-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot



TEST NUMBER: P865515

CATALOG NUMBER: PRLX-2001-S-935-15L-L-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	61	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	38	33	32
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	10691
5°	10688
10°	10586
15°	10472
20°	10294
25°	10087
30°	9891
35°	9647
40°	9392
45°	9141
50°	8850
55°	8221
60°	6332
65°	3354
70°	1941
75°	1966
80°	2170
85°	2545

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9141 cd/sqm

TEST NUMBER: P865515

CATALOG NUMBER: PRLX-2001-S-935-15L-L-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.9	4.1
10°-20°	174.6	11.6
20°-30°	258.3	17.2
30°-40°	303.1	20.2
40°-50°	305.7	20.4
50°-60°	252.3	16.8
60°-70°	97.2	6.5
70°-80°	33.1	2.2
80°-90°	13.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.8	33.0
0°-40°	797.9	53.2
0°-60°	1355.8	90.4
0°-90°	1500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1500.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	656	
5°	653	62
15°	620	175
25°	560	258
35°	484	303
45°	396	306
55°	289	252
65°	87	97
75°	31	33
85°	14	14
90°	0	

TEST NUMBER: P865515

CATALOG NUMBER: PRLX-2001-S-935-15L-L-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	655.5
2.5°	655.5
5°	652.8
7.5°	647.4
10°	639.2
12.5°	629.7
15°	620.2
17.5°	606.6
20°	593.1
22.5°	578.1
25°	560.5
27.5°	542.9
30°	525.2
32.5°	506.2
35°	484.5
37.5°	462.8
40°	441.1
42.5°	419.4
45°	396.3
47.5°	373.2
50°	348.8
52.5°	321.6
55°	289.1
57.5°	248.4
60°	194.1
62.5°	135.7
65°	86.9
67.5°	55.6
70°	40.7
72.5°	35.3
75°	31.2
77.5°	27.1
80°	23.1
82.5°	19.0
85°	13.6
87.5°	6.8
90°	0.0



TEST NUMBER: P865515  
 CATALOG NUMBER: PRLX-2001-S-935-15L-L-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.29	20.80	19.65	21.11	21.43	19.29	20.80	19.65	21.11	21.43
	3H	19.43	20.77	19.81	21.10	21.46	19.43	20.77	19.81	21.10	21.46
	4H	19.49	20.75	19.89	21.09	21.47	19.49	20.75	19.89	21.09	21.47
	6H	19.57	20.73	19.98	21.10	21.49	19.57	20.73	19.98	21.10	21.49
	8H	19.61	20.72	20.04	21.11	21.51	19.61	20.72	20.04	21.11	21.51
	12H	19.66	20.71	20.09	21.09	21.52	19.66	20.71	20.09	21.09	21.52
4H	2H	19.32	20.58	19.72	20.93	21.31	19.32	20.58	19.72	20.93	21.31
	3H	19.54	20.57	19.95	20.97	21.37	19.54	20.57	19.95	20.97	21.37
	4H	19.66	20.58	20.09	20.99	21.43	19.66	20.58	20.09	20.99	21.43
	6H	19.83	20.63	20.29	21.07	21.53	19.83	20.63	20.29	21.07	21.53
	8H	19.91	20.66	20.38	21.10	21.57	19.91	20.66	20.38	21.10	21.57
	12H	20.00	20.67	20.48	21.15	21.62	20.00	20.67	20.48	21.15	21.62
8H	4H	19.65	20.40	20.12	20.84	21.31	19.65	20.40	20.12	20.84	21.31
	6H	19.89	20.51	20.39	21.00	21.48	19.89	20.51	20.39	21.00	21.48
	8H	20.03	20.59	20.54	21.10	21.59	20.03	20.59	20.54	21.10	21.59
	12H	20.19	20.69	20.70	21.18	21.75	20.19	20.69	20.70	21.18	21.75
12H	4H	19.64	20.31	20.12	20.79	21.26	19.64	20.31	20.12	20.79	21.26
	6H	19.88	20.44	20.40	20.95	21.44	19.88	20.44	20.40	20.95	21.44
	8H	20.07	20.57	20.58	21.06	21.63	20.07	20.57	20.58	21.06	21.63