

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865523

Luminaire Tested: PRLX-2001-S-935-20L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-935-20L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2000.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.31
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865523

CATALOG NUMBER: PRLX-2001-S-935-20L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865523

CATALOG NUMBER: PRLX-2001-S-935-20L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	61	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	38	33	32
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14255
5°	14251
10°	14116
15°	13964
20°	13726
25°	13449
30°	13189
35°	12862
40°	12521
45°	12188
50°	11801
55°	10959
60°	8442
65°	4469
70°	2589
75°	2622
80°	2893
85°	3387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12188 cd/sqm

TEST NUMBER: P865523

CATALOG NUMBER: PRLX-2001-S-935-20L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	4.1
10°-20°	232.8	11.6
20°-30°	344.5	17.2
30°-40°	404.2	20.2
40°-50°	407.5	20.4
50°-60°	336.4	16.8
60°-70°	129.6	6.5
70°-80°	44.2	2.2
80°-90°	18.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.7	33.0
0°-40°	1063.9	53.2
0°-60°	1807.8	90.4
0°-90°	2000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	874	
5°	870	82
15°	827	233
25°	747	344
35°	646	404
45°	528	408
55°	385	336
65°	116	130
75°	42	44
85°	18	18
90°	0	

TEST NUMBER: P865523

CATALOG NUMBER: PRLX-2001-S-935-20L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	874.0
2.5°	874.0
5°	870.4
7.5°	863.1
10°	852.3
12.5°	839.6
15°	827.0
17.5°	808.9
20°	790.8
22.5°	770.9
25°	747.3
27.5°	723.8
30°	700.3
32.5°	675.0
35°	646.0
37.5°	617.1
40°	588.1
42.5°	559.1
45°	528.4
47.5°	497.6
50°	465.1
52.5°	428.9
55°	385.4
57.5°	331.1
60°	258.8
62.5°	181.0
65°	115.8
67.5°	74.2
70°	54.3
72.5°	47.0
75°	41.6
77.5°	36.2
80°	30.8
82.5°	25.3
85°	18.1
87.5°	9.0
90°	0.0



TEST NUMBER: P865523
 CATALOG NUMBER: PRLX-2001-S-935-20L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.28	21.80	20.65	22.11	22.43	20.28	21.80	20.65	22.11	22.43
	3H	20.43	21.77	20.80	22.10	22.46	20.43	21.77	20.80	22.10	22.46
	4H	20.49	21.74	20.89	22.09	22.47	20.49	21.74	20.89	22.09	22.47
	6H	20.57	21.73	20.98	22.09	22.49	20.57	21.73	20.98	22.09	22.49
	8H	20.61	21.71	21.04	22.10	22.51	20.61	21.71	21.04	22.10	22.51
	12H	20.65	21.71	21.09	22.09	22.52	20.65	21.71	21.09	22.09	22.52
4H	2H	20.32	21.58	20.72	21.93	22.31	20.32	21.58	20.72	21.93	22.31
	3H	20.54	21.57	20.95	21.97	22.37	20.54	21.57	20.95	21.97	22.37
	4H	20.66	21.58	21.09	21.99	22.43	20.66	21.58	21.09	21.99	22.43
	6H	20.83	21.62	21.28	22.07	22.53	20.83	21.62	21.28	22.07	22.53
	8H	20.91	21.66	21.37	22.10	22.57	20.91	21.66	21.37	22.10	22.57
	12H	21.00	21.66	21.48	22.14	22.62	21.00	21.66	21.48	22.14	22.62
8H	4H	20.65	21.40	21.12	21.84	22.31	20.65	21.40	21.12	21.84	22.31
	6H	20.89	21.50	21.38	22.00	22.48	20.89	21.50	21.38	22.00	22.48
	8H	21.03	21.58	21.54	22.10	22.58	21.03	21.58	21.54	22.10	22.58
	12H	21.19	21.69	21.70	22.18	22.74	21.19	21.69	21.70	22.18	22.74
12H	4H	20.64	21.31	21.12	21.78	22.26	20.64	21.31	21.12	21.78	22.26
	6H	20.88	21.44	21.40	21.95	22.44	20.88	21.44	21.40	21.95	22.44
	8H	21.07	21.57	21.58	22.06	22.63	21.07	21.57	21.58	22.06	22.63