

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865532

Luminaire Tested: PRLX-2001-S-940-05L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865532  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-940-05L-G-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 157.2 lumens  
Efficiency: N/A  
Efficacy: 25.4 lumens/watt  
Spacing Criteria (0/90/45): 1.52 / 1.52 / 1.69  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 6.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865532

CATALOG NUMBER: PRLX-2001-S-940-05L-G-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865532

CATALOG NUMBER: PRLX-2001-S-940-05L-G-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	107	102	97	92	104	99	95	91	95	91	88		91	88	85		87	85	82	80
2	96	87	79	73	93	85	78	72	81	75	70		78	73	68		75	71	67	64
3	87	75	66	59	84	73	65	58	70	63	57		67	61	56		65	60	55	53
4	79	66	56	49	76	64	55	48	62	54	47		59	52	47		57	51	46	44
5	72	58	48	41	70	57	48	41	55	46	40		53	45	40		51	44	39	37
6	66	52	42	35	64	51	42	35	49	41	35		47	40	34		45	39	34	32
7	61	46	37	30	59	46	37	30	44	36	30		43	35	30		41	35	30	27
8	57	42	33	27	55	41	33	27	40	32	27		39	32	26		37	31	26	24
9	53	38	30	24	51	38	29	24	37	29	24		35	28	23		34	28	23	21
10	49	35	27	21	48	35	27	21	34	26	21		33	26	21		32	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	610
5°	614
10°	626
15°	640
20°	656
25°	675
30°	702
35°	739
40°	784
45°	842
50°	901
55°	930
60°	939
65°	934
70°	925
75°	907
80°	902
85°	992

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 87.5°  
 Luminance: 1309 cd/sqm

TEST NUMBER: P865532

CATALOG NUMBER: PRLX-2001-S-940-05L-G-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	3.6	2.3
10°-20°	10.7	6.8
20°-30°	17.4	11.1
30°-40°	23.3	14.8
40°-50°	28.2	17.9
50°-60°	29.1	18.5
60°-70°	24.0	15.2
70°-80°	15.2	9.7
80°-90°	5.7	3.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	31.7	20.2
0°-40°	55.0	35.0
0°-60°	112.2	71.4
0°-90°	157.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	37	
5°	38	4
15°	38	11
25°	38	17
35°	37	23
45°	36	28
55°	33	29
65°	24	24
75°	14	15
85°	5	6
90°	0	

TEST NUMBER: P865532

CATALOG NUMBER: PRLX-2001-S-940-05L-G-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	37.4
2.5°	37.4
5°	37.5
7.5°	37.7
10°	37.8
12.5°	37.9
15°	37.9
17.5°	37.8
20°	37.8
22.5°	37.7
25°	37.5
27.5°	37.5
30°	37.3
32.5°	37.2
35°	37.1
37.5°	37.0
40°	36.8
42.5°	36.7
45°	36.5
47.5°	36.2
50°	35.5
52.5°	34.3
55°	32.7
57.5°	30.8
60°	28.8
62.5°	26.6
65°	24.2
67.5°	21.9
70°	19.4
72.5°	16.9
75°	14.4
77.5°	12.0
80°	9.6
82.5°	7.4
85°	5.3
87.5°	3.5
90°	0.0



TEST NUMBER: P865532

CATALOG NUMBER: PRLX-2001-S-940-05L-G-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.37	14.14	12.74	14.45	14.77	12.37	14.14	12.74	14.45	14.77
	3H	14.45	16.07	14.83	16.39	16.75	14.45	16.07	14.83	16.39	16.75
	4H	15.29	16.81	15.68	17.16	17.53	15.29	16.81	15.68	17.16	17.53
	6H	15.98	17.40	16.39	17.76	18.15	15.98	17.40	16.39	17.76	18.15
	8H	16.25	17.61	16.67	18.00	18.40	16.25	17.61	16.67	18.00	18.40
	12H	16.49	17.79	16.91	18.18	18.60	16.49	17.79	16.91	18.18	18.60
4H	2H	13.10	14.62	13.49	14.97	15.34	13.10	14.62	13.49	14.97	15.34
	3H	15.41	16.70	15.81	17.10	17.50	15.41	16.70	15.81	17.10	17.50
	4H	16.38	17.56	16.81	17.97	18.41	16.38	17.56	16.81	17.97	18.41
	6H	17.23	18.27	17.67	18.70	19.15	17.23	18.27	17.67	18.70	19.15
	8H	17.57	18.54	18.02	18.98	19.45	17.57	18.54	18.02	18.98	19.45
	12H	17.88	18.76	18.35	19.23	19.70	17.88	18.76	18.35	19.23	19.70
8H	4H	16.79	17.77	17.25	18.21	18.67	16.79	17.77	17.25	18.21	18.67
	6H	17.79	18.62	18.28	19.10	19.57	17.79	18.62	18.28	19.10	19.57
	8H	18.24	18.98	18.74	19.48	19.96	18.24	18.98	18.74	19.48	19.96
	12H	18.67	19.33	19.17	19.81	20.37	18.67	19.33	19.17	19.81	20.37
12H	4H	16.86	17.74	17.33	18.22	18.68	16.86	17.74	17.33	18.22	18.68
	6H	17.90	18.64	18.40	19.14	19.62	17.90	18.64	18.40	19.14	19.62
	8H	18.42	19.08	18.92	19.57	20.12	18.42	19.08	18.92	19.57	20.12