

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246987

Luminaire Tested: **LD8B90D010 ER8B90950 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B90D010 ER8B90950 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8934.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246987

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P246987

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	452091
5°	433243
10°	382022
15°	321951
20°	264341
25°	214253
30°	158614
35°	95477
40°	42520
45°	16532
50°	5929
55°	1731
60°	1215
65°	912
70°	90
75°	500
80°	0
85°	1486



TEST NUMBER: P246987

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1277.8	14.3
10°-20°	2801.1	31.4
20°-30°	2856.7	32.0
30°-40°	1599.9	17.9
40°-50°	341.2	3.8
50°-60°	42.2	0.5
60°-70°	11.0	0.1
70°-80°	2.6	0.0
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6935.6	77.6
0°-40°	8535.5	95.5
0°-60°	8918.9	99.8
0°-90°	8934.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8934.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14661	
5°	13996	###
15°	10085	2801
25°	6297	2857
35°	2536	1600
45°	379	341
55°	32	42
65°	12	11
75°	4	3
85°	4	1
90°	0	



TEST NUMBER: P246987

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	14661.0
2.5°	14495.8
5°	13996.3
7.5°	13192.4
10°	12200.5
12.5°	11135.9
15°	10084.9
17.5°	9027.6
20°	8055.4
22.5°	7150.8
25°	6297.1
27.5°	5400.8
30°	4454.6
32.5°	3465.8
35°	2536.3
37.5°	1699.2
40°	1056.3
42.5°	631.5
45°	379.1
47.5°	210.8
50°	123.6
52.5°	65.4
55°	32.2
57.5°	22.8
60°	19.7
62.5°	9.3
65°	12.5
67.5°	12.5
70°	1.0
72.5°	3.1
75°	4.2
77.5°	2.1
80°	0.0
82.5°	1.0
85°	4.2
87.5°	0.0
90°	0.0

(END OF REPORT)