

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865536

Luminaire Tested: PRLX-2001-S-940-05L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-940-05L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 417.1 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.29
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865536

CATALOG NUMBER: PRLX-2001-S-940-05L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P865536

CATALOG NUMBER: PRLX-2001-S-940-05L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	88	78	70	64	86	77	70	64	74	68	63	72	67	62	70	65	62	60
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	64	59	54	53
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42
8	66	53	45	40	64	52	45	40	51	44	40	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3242
5°	3240
10°	3216
15°	3159
20°	3102
25°	3040
30°	2944
35°	2851
40°	2749
45°	2643
50°	2530
55°	2340
60°	1647
65°	540
70°	43
75°	32
80°	47
85°	94

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2643 cd/sqm

TEST NUMBER: P865536

CATALOG NUMBER: PRLX-2001-S-940-05L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.8	4.5
10°-20°	52.7	12.6
20°-30°	77.5	18.6
30°-40°	89.5	21.4
40°-50°	88.4	21.2
50°-60°	70.9	17.0
60°-70°	18.3	4.4
70°-80°	0.6	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.0	35.7
0°-40°	238.5	57.2
0°-60°	397.7	95.3
0°-90°	417.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	417.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	199	
5°	198	19
15°	187	53
25°	169	78
35°	143	89
45°	115	88
55°	82	71
65°	14	18
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P865536

CATALOG NUMBER: PRLX-2001-S-940-05L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	198.8
2.5°	198.4
5°	197.9
7.5°	196.5
10°	194.2
12.5°	190.4
15°	187.1
17.5°	182.9
20°	178.7
22.5°	173.6
25°	168.9
27.5°	162.4
30°	156.3
32.5°	149.7
35°	143.2
37.5°	136.2
40°	129.1
42.5°	122.1
45°	114.6
47.5°	107.1
50°	99.7
52.5°	91.7
55°	82.3
57.5°	68.8
60°	50.5
62.5°	30.4
65°	14.0
67.5°	5.1
70°	0.9
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0



TEST NUMBER: P865536

CATALOG NUMBER: PRLX-2001-S-940-05L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.87	16.32	15.23	16.63	16.95	14.87	16.32	15.23	16.63	16.95
	3H	14.77	16.04	15.14	16.37	16.74	14.77	16.04	15.14	16.37	16.74
	4H	14.70	15.89	15.10	16.24	16.62	14.70	15.89	15.10	16.24	16.62
	6H	14.63	15.72	15.05	16.09	16.48	14.63	15.72	15.05	16.09	16.48
	8H	14.59	15.63	15.02	16.02	16.42	14.59	15.63	15.02	16.02	16.42
	12H	14.56	15.55	14.99	15.93	16.36	14.56	15.55	14.99	15.93	16.36
4H	2H	14.77	15.96	15.17	16.31	16.69	14.77	15.96	15.17	16.31	16.69
	3H	14.67	15.63	15.09	16.03	16.44	14.67	15.63	15.09	16.03	16.44
	4H	14.60	15.45	15.03	15.87	16.31	14.60	15.45	15.03	15.87	16.31
	6H	14.53	15.26	14.99	15.70	16.17	14.53	15.26	14.99	15.70	16.17
	8H	14.48	15.16	14.94	15.61	16.08	14.48	15.16	14.94	15.61	16.08
	12H	14.44	15.04	14.92	15.52	16.00	14.44	15.04	14.92	15.52	16.00
8H	4H	14.47	15.16	14.94	15.60	16.07	14.47	15.16	14.94	15.60	16.07
	6H	14.38	14.94	14.88	15.44	15.92	14.38	14.94	14.88	15.44	15.92
	8H	14.32	14.83	14.84	15.34	15.83	14.32	14.83	14.84	15.34	15.83
	12H	14.27	14.73	14.79	15.22	15.79	14.27	14.73	14.79	15.22	15.79
12H	4H	14.43	15.04	14.92	15.52	15.99	14.43	15.04	14.92	15.52	15.99
	6H	14.31	14.82	14.83	15.34	15.83	14.31	14.82	14.83	15.34	15.83
	8H	14.27	14.73	14.78	15.22	15.79	14.27	14.73	14.78	15.22	15.79