

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250352

Luminaire Tested: **LD8B90D010 ER8B90950 8LBN0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B90D010 ER8B90950 8LBN0GPH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7047.0 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 86.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250352

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBN0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250352

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBN0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	347229
5°	341681
10°	303576
15°	250425
20°	210907
25°	177888
30°	133194
35°	75379
40°	29804
45°	8002
50°	1535
55°	0
60°	222
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250352

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBN0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1010.8	14.3
10°-20°	2197.0	31.2
20°-30°	2358.7	33.5
30°-40°	1274.8	18.1
40°-50°	198.9	2.8
50°-60°	5.5	0.1
60°-70°	1.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5566.5	79.0
0°-40°	6841.3	97.1
0°-60°	7045.7	100.0
0°-90°	7047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7047.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11260	
5°	11038	###
15°	7844	2197
25°	5228	2359
35°	2002	1275
45°	184	199
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250352

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBN0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	11260.4
1°	11281.8
2°	11271.2
3°	11232.6
4°	11158.4
5°	11038.3
6°	10873.0
7°	10650.5
8°	10372.1
9°	10051.6
10°	9695.2
11°	9321.4
12°	8933.6
13°	8546.2
14°	8186.2
15°	7844.4
16°	7530.5
17°	7227.3
18°	6945.2
19°	6681.1
20°	6427.1
21°	6180.2
22°	5947.4
23°	5715.0
24°	5471.8
25°	5228.3
26°	4981.4
27°	4699.6
28°	4389.2
29°	4072.3
30°	3740.7
31°	3384.6
32°	3028.3
33°	2675.8
34°	2319.8
35°	2002.4
37.5°	1279.7
40°	740.4
42.5°	395.0
45°	183.5
47.5°	98.9
50°	32.0
52.5°	3.6
55°	0.0
57.5°	3.6



TEST NUMBER: P250352

CATALOG NUMBER: LD8B90D010 ER8B90950 8LBN0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	3.6
62.5°	0.0
65°	0.0
67.5°	3.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)