

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865569

Luminaire Tested: PRLX-2001-S-940-25L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-940-25L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2190.8 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.28
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865569

CATALOG NUMBER: PRLX-2001-S-940-25L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot



TEST NUMBER: P865569

CATALOG NUMBER: PRLX-2001-S-940-25L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	75	63	55	50	74	62	55	49	61	54	49	59	53	49	58	52	48	46
7	70	58	50	44	68	57	49	44	56	49	44	54	48	43	53	47	43	41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17055
5°	17006
10°	16815
15°	16472
20°	16161
25°	15745
30°	15332
35°	14812
40°	14295
45°	13759
50°	13177
55°	12040
60°	8547
65°	3250
70°	782
75°	737
80°	883
85°	1310

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13759 cd/sqm

TEST NUMBER: P865569

CATALOG NUMBER: PRLX-2001-S-940-25L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.3	4.5
10°-20°	275.2	12.6
20°-30°	403.4	18.4
30°-40°	465.4	21.2
40°-50°	459.7	21.0
50°-60°	367.2	16.8
60°-70°	103.8	4.7
70°-80°	12.1	0.6
80°-90°	5.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.9	35.5
0°-40°	1242.3	56.7
0°-60°	2069.2	94.5
0°-90°	2190.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2190.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1046	
5°	1039	98
15°	976	275
25°	875	403
35°	744	465
45°	596	460
55°	423	367
65°	84	104
75°	12	12
85°	7	6
90°	0	

TEST NUMBER: P865569

CATALOG NUMBER: PRLX-2001-S-940-25L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1045.7
2.5°	1045.7
5°	1038.7
7.5°	1027.0
10°	1015.3
12.5°	996.6
15°	975.5
17.5°	954.5
20°	931.1
22.5°	905.3
25°	874.9
27.5°	846.9
30°	814.1
32.5°	779.0
35°	743.9
37.5°	708.8
40°	671.4
42.5°	634.0
45°	596.5
47.5°	556.8
50°	519.3
52.5°	477.2
55°	423.4
57.5°	355.6
60°	262.0
62.5°	163.8
65°	84.2
67.5°	37.4
70°	16.4
72.5°	11.7
75°	11.7
77.5°	9.4
80°	9.4
82.5°	7.0
85°	7.0
87.5°	2.3
90°	0.0



TEST NUMBER: P865569

CATALOG NUMBER: PRLX-2001-S-940-25L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.51	21.97	20.87	22.28	22.60	20.51	21.97	20.87	22.28	22.60
	3H	20.43	21.72	20.81	22.05	22.41	20.43	21.72	20.81	22.05	22.41
	4H	20.38	21.58	20.78	21.93	22.31	20.38	21.58	20.78	21.93	22.31
	6H	20.32	21.42	20.73	21.79	22.18	20.32	21.42	20.73	21.79	22.18
	8H	20.29	21.33	20.72	21.72	22.13	20.29	21.33	20.72	21.72	22.13
	12H	20.26	21.26	20.69	21.64	22.07	20.26	21.26	20.69	21.64	22.07
4H	2H	20.44	21.64	20.84	21.99	22.37	20.44	21.64	20.84	21.99	22.37
	3H	20.37	21.34	20.78	21.74	22.15	20.37	21.34	20.78	21.74	22.15
	4H	20.31	21.17	20.74	21.59	22.03	20.31	21.17	20.74	21.59	22.03
	6H	20.26	21.00	20.72	21.45	21.91	20.26	21.00	20.72	21.45	21.91
	8H	20.22	20.91	20.68	21.36	21.83	20.22	20.91	20.68	21.36	21.83
	12H	20.19	20.81	20.68	21.29	21.76	20.19	20.81	20.68	21.29	21.76
8H	4H	20.19	20.89	20.66	21.34	21.80	20.19	20.89	20.66	21.34	21.80
	6H	20.13	20.70	20.63	21.19	21.67	20.13	20.70	20.63	21.19	21.67
	8H	20.08	20.60	20.60	21.12	21.61	20.08	20.60	20.60	21.12	21.61
	12H	20.07	20.53	20.58	21.03	21.59	20.07	20.53	20.58	21.03	21.59
12H	4H	20.16	20.77	20.64	21.25	21.73	20.16	20.77	20.64	21.25	21.73
	6H	20.07	20.59	20.59	21.10	21.59	20.07	20.59	20.59	21.10	21.59
	8H	20.05	20.51	20.56	21.00	21.57	20.05	20.51	20.56	21.00	21.57