

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250359

Luminaire Tested: **LD8B90D010 ER8B909727 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B90D010 ER8B909727 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5321.0 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250359

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250359

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250359

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	763.3	14.3
10°-20°	1658.9	31.2
20°-30°	1781.0	33.5
30°-40°	962.6	18.1
40°-50°	150.2	2.8
50°-60°	4.1	0.1
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4203.1	79.0
0°-40°	5165.7	97.1
0°-60°	5320.0	100.0
0°-90°	5321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5321.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8502	
5°	8335	763
15°	5923	1659
25°	3948	1781
35°	1512	963
45°	138	150
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250359

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	8502.4
1°	8518.6
2°	8510.6
3°	8481.4
4°	8425.4
5°	8334.7
6°	8209.9
7°	8041.9
8°	7831.7
9°	7589.7
10°	7320.6
11°	7038.3
12°	6745.5
13°	6453.0
14°	6181.2
15°	5923.1
16°	5686.1
17°	5457.1
18°	5244.2
19°	5044.7
20°	4852.9
21°	4666.5
22°	4490.7
23°	4315.3
24°	4131.6
25°	3947.8
26°	3761.4
27°	3548.5
28°	3314.1
29°	3074.9
30°	2824.5
31°	2555.7
32°	2286.6
33°	2020.4
34°	1751.6
35°	1511.9
37.5°	966.3
40°	559.1
42.5°	298.2
45°	138.5
47.5°	74.7
50°	24.1
52.5°	2.7
55°	0.0
57.5°	2.7



TEST NUMBER: P250359

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
60°	2.7
62.5°	0.0
65°	0.0
67.5°	2.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)