

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866932

Luminaire Tested: PRLX-2002-L-927-133L-L-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866932  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-83)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-L-927-133L-L-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9503.2 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 111.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866932

CATALOG NUMBER: PRLX-2002-L-927-133L-L-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866932

CATALOG NUMBER: PRLX-2002-L-927-133L-L-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56
6	78	66	59	53	76	66	58	53	64	57	53	62	57	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24790
5°	24720
10°	24454
15°	24090
20°	23671
25°	23188
30°	22559
35°	21746
40°	20665
45°	19349
50°	17637
55°	11792
60°	4190
65°	969
70°	156
75°	164
80°	213
85°	243

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19349 cd/sqm

TEST NUMBER: P866932

CATALOG NUMBER: PRLX-2002-L-927-133L-L-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	472.9	5.0
10°-20°	1329.2	14.0
20°-30°	1960.1	20.6
30°-40°	2252.4	23.7
40°-50°	2132.4	22.4
50°-60°	1214.1	12.8
60°-70°	128.7	1.4
70°-80°	9.2	0.1
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3762.2	39.6
0°-40°	6014.6	63.3
0°-60°	9361.0	98.5
0°-90°	9503.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9503.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5025	
5°	4991	473
15°	4716	1329
25°	4259	1960
35°	3610	2252
45°	2773	2132
55°	1371	1214
65°	83	129
75°	9	9
85°	4	4
90°	0	

TEST NUMBER: P866932

CATALOG NUMBER: PRLX-2002-L-927-133L-L-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5024.6
2.5°	5019.2
5°	4991.2
7.5°	4944.8
10°	4881.2
12.5°	4803.6
15°	4716.3
17.5°	4617.2
20°	4508.3
22.5°	4389.8
25°	4259.4
27.5°	4119.3
30°	3959.7
32.5°	3791.6
35°	3610.5
37.5°	3414.4
40°	3208.5
42.5°	3000.5
45°	2773.1
47.5°	2537.1
50°	2297.8
52.5°	1940.0
55°	1370.9
57.5°	818.0
60°	424.6
62.5°	212.3
65°	83.0
67.5°	16.2
70°	10.8
72.5°	9.7
75°	8.6
77.5°	7.5
80°	7.5
82.5°	5.4
85°	4.3
87.5°	2.2
90°	0.0



TEST NUMBER: P866932  
 CATALOG NUMBER: PRLX-2002-L-927-133L-L-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.05	18.41	17.41	18.72	19.04	17.05	18.41	17.41	18.72	19.04
	3H	16.92	18.12	17.30	18.45	18.81	16.92	18.12	17.30	18.45	18.81
	4H	16.86	17.96	17.26	18.31	18.70	16.86	17.96	17.26	18.31	18.70
	6H	16.78	17.79	17.19	18.16	18.56	16.78	17.79	17.19	18.16	18.56
	8H	16.74	17.70	17.17	18.09	18.49	16.74	17.70	17.17	18.09	18.49
	12H	16.70	17.61	17.13	18.00	18.43	16.70	17.61	17.13	18.00	18.43
4H	2H	16.88	17.98	17.28	18.33	18.72	16.88	17.98	17.28	18.33	18.72
	3H	16.75	17.64	17.17	18.05	18.45	16.75	17.64	17.17	18.05	18.45
	4H	16.67	17.46	17.10	17.88	18.32	16.67	17.46	17.10	17.88	18.32
	6H	16.59	17.27	17.05	17.71	18.18	16.59	17.27	17.05	17.71	18.18
	8H	16.53	17.17	17.00	17.61	18.08	16.53	17.17	17.00	17.61	18.08
	12H	16.48	17.05	16.97	17.53	18.00	16.48	17.05	16.97	17.53	18.00
8H	4H	16.53	17.16	17.00	17.61	18.08	16.53	17.16	17.00	17.61	18.08
	6H	16.42	16.95	16.93	17.44	17.92	16.42	16.95	16.93	17.44	17.92
	8H	16.36	16.83	16.88	17.35	17.84	16.36	16.83	16.88	17.35	17.84
	12H	16.31	16.73	16.82	17.23	17.80	16.31	16.73	16.82	17.23	17.80
12H	4H	16.48	17.04	16.97	17.52	18.00	16.48	17.04	16.97	17.52	18.00
	6H	16.36	16.83	16.88	17.35	17.84	16.36	16.83	16.88	17.35	17.84
	8H	16.31	16.73	16.82	17.23	17.80	16.31	16.73	16.82	17.23	17.80