

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249855

Luminaire Tested: **LD8B90D010 ER8B909727 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B90D010 ER8B909727 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5912.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249855

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249855

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249855

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	739.4	12.5
10°-20°	1735.9	29.4
20°-30°	1897.3	32.1
30°-40°	1129.1	19.1
40°-50°	309.7	5.2
50°-60°	70.1	1.2
60°-70°	21.7	0.4
70°-80°	6.6	0.1
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4372.7	74.0
0°-40°	5501.7	93.1
0°-60°	5881.6	99.5
0°-90°	5912.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5912.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8109	
5°	7979	739
15°	6230	1736
25°	4191	1897
35°	1787	1129
45°	362	310
55°	70	70
65°	22	22
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P249855

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	8108.7
1°	8124.7
2°	8114.7
3°	8094.7
4°	8048.7
5°	7978.6
6°	7888.6
7°	7768.6
8°	7628.5
9°	7466.5
10°	7284.4
11°	7090.4
12°	6882.3
13°	6668.2
14°	6446.1
15°	6230.1
16°	6018.0
17°	5809.9
18°	5601.9
19°	5393.8
20°	5191.7
22.5°	4683.6
25°	4191.4
27.5°	3649.2
30°	3047.0
32.5°	2400.8
35°	1786.6
37.5°	1242.4
40°	824.3
42.5°	540.2
45°	362.1
47.5°	240.1
50°	160.1
52.5°	98.0
55°	70.0
57.5°	50.0
60°	38.0
62.5°	28.0
65°	22.0
67.5°	14.0
70°	10.0
72.5°	8.0
75°	6.0
77.5°	4.0
80°	4.0



TEST NUMBER: P249855

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	2.0
85°	2.0
87.5°	2.0
90°	0.0

(END OF REPORT)