

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866940

Luminaire Tested: PRLX-2002-L-927-15L-L-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-83)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-L-927-15L-L-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1074.5 lumens  
Efficiency: N/A  
Efficacy: 65.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 16.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866940

CATALOG NUMBER: PRLX-2002-L-927-15L-L-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866940

CATALOG NUMBER: PRLX-2002-L-927-15L-L-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66		75	70	66		73	68	65	63
5	84	73	65	60	82	72	65	60	70	64	59		68	63	58		66	62	58	56
6	78	66	59	53	76	66	58	53	64	57	53		62	57	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56	51	47	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	43		52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36		45	40	35		45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2803
5°	2795
10°	2765
15°	2724
20°	2676
25°	2622
30°	2551
35°	2459
40°	2337
45°	2187
50°	1994
55°	1333
60°	474
65°	110
70°	17
75°	19
80°	26
85°	28

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2187 cd/sqm

TEST NUMBER: P866940

CATALOG NUMBER: PRLX-2002-L-927-15L-L-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.5	5.0
10°-20°	150.3	14.0
20°-30°	221.6	20.6
30°-40°	254.7	23.7
40°-50°	241.1	22.4
50°-60°	137.3	12.8
60°-70°	14.5	1.4
70°-80°	1.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.4	39.6
0°-40°	680.0	63.3
0°-60°	1058.4	98.5
0°-90°	1074.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1074.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	568	
5°	564	53
15°	533	150
25°	482	222
35°	408	255
45°	314	241
55°	155	137
65°	9	15
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P866940

CATALOG NUMBER: PRLX-2002-L-927-15L-L-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	568.1
2.5°	567.5
5°	564.3
7.5°	559.1
10°	551.9
12.5°	543.1
15°	533.3
17.5°	522.0
20°	509.7
22.5°	496.3
25°	481.6
27.5°	465.7
30°	447.7
32.5°	428.7
35°	408.2
37.5°	386.0
40°	362.8
42.5°	339.3
45°	313.5
47.5°	286.9
50°	259.8
52.5°	219.3
55°	155.0
57.5°	92.5
60°	48.0
62.5°	24.0
65°	9.4
67.5°	1.8
70°	1.2
72.5°	1.1
75°	1.0
77.5°	0.9
80°	0.9
82.5°	0.6
85°	0.5
87.5°	0.2
90°	0.0



TEST NUMBER: P866940  
 CATALOG NUMBER: PRLX-2002-L-927-15L-L-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.48	10.84	9.84	11.15	11.47	9.48	10.84	9.84	11.15	11.47
	3H	9.35	10.55	9.73	10.88	11.24	9.35	10.55	9.73	10.88	11.24
	4H	9.28	10.39	9.69	10.74	11.12	9.28	10.39	9.69	10.74	11.12
	6H	9.21	10.22	9.62	10.59	10.99	9.21	10.22	9.62	10.59	10.99
	8H	9.17	10.13	9.60	10.52	10.92	9.17	10.13	9.60	10.52	10.92
	12H	9.13	10.04	9.56	10.43	10.86	9.13	10.04	9.56	10.43	10.86
4H	2H	9.30	10.41	9.71	10.76	11.15	9.30	10.41	9.71	10.76	11.15
	3H	9.18	10.07	9.59	10.47	10.88	9.18	10.07	9.59	10.47	10.88
	4H	9.10	9.88	9.53	10.30	10.75	9.10	9.88	9.53	10.30	10.75
	6H	9.02	9.69	9.48	10.14	10.61	9.02	9.69	9.48	10.14	10.61
	8H	8.96	9.59	9.43	10.04	10.51	8.96	9.59	9.43	10.04	10.51
	12H	8.91	9.47	9.40	9.96	10.43	8.91	9.47	9.40	9.96	10.43
8H	4H	8.96	9.59	9.43	10.04	10.51	8.96	9.59	9.43	10.04	10.51
	6H	8.85	9.37	9.35	9.87	10.35	8.85	9.37	9.35	9.87	10.35
	8H	8.78	9.26	9.31	9.77	10.27	8.78	9.26	9.31	9.77	10.27
	12H	8.73	9.16	9.25	9.66	10.23	8.73	9.16	9.25	9.66	10.23
12H	4H	8.91	9.47	9.39	9.95	10.43	8.91	9.47	9.39	9.95	10.43
	6H	8.78	9.26	9.31	9.77	10.27	8.78	9.26	9.31	9.77	10.27
	8H	8.73	9.16	9.25	9.65	10.23	8.73	9.16	9.25	9.65	10.23