

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250107

Luminaire Tested: **LD8B90D010 ER8B909727 8LBN0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250107  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13946)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B90D010 ER8B909727 8LBN0WH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6099.0 lumens  
Efficiency: N/A  
Efficacy: 70.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.66  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 86.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250107

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P250107

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89		92	90	87		90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78		84	81	78		83	80	77	76
6	92	84	79	75	90	83	78	74	82	77	74		80	76	74		79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70		77	73	70		76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67		73	69	66		72	69	66	65
9	81	72	67	64	80	72	67	64	71	66	63		70	66	63		69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60		67	63	60		67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250107

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1070.8	17.6
10°-20°	2074.9	34.0
20°-30°	1868.1	30.6
30°-40°	924.3	15.2
40°-50°	140.6	2.3
50°-60°	5.7	0.1
60°-70°	7.4	0.1
70°-80°	2.8	0.0
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5013.8	82.2
0°-40°	5938.0	97.4
0°-60°	6084.4	99.8
0°-90°	6099.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6099.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12260	
5°	11811	###
15°	7434	2075
25°	4131	1868
35°	1496	924
45°	155	141
55°	2	6
65°	4	7
75°	4	3
85°	6	4
90°	0	



TEST NUMBER: P250107

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12260.5
1°	12235.0
2°	12241.3
3°	12179.6
4°	12066.8
5°	11811.4
6°	11615.6
7°	11304.9
8°	10887.8
9°	10453.6
10°	9930.1
11°	9461.9
12°	8959.7
13°	8404.2
14°	7925.4
15°	7433.7
16°	7014.5
17°	6644.2
18°	6188.7
19°	5854.6
20°	5526.9
21°	5186.3
22°	4937.4
23°	4647.9
24°	4381.9
25°	4130.8
26°	3834.9
27°	3569.0
28°	3330.6
29°	3068.8
30°	2692.1
31°	2479.4
32°	2211.2
33°	1917.5
34°	1694.0
35°	1496.1
37.5°	947.0
40°	427.8
42.5°	291.6
45°	155.3
47.5°	87.2
50°	2.1
52.5°	8.5
55°	2.1
57.5°	12.8



TEST NUMBER: P250107

CATALOG NUMBER: LD8B90D010 ER8B909727 8LBN0WH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.1
62.5°	10.7
65°	4.3
67.5°	10.7
70°	6.4
72.5°	2.1
75°	4.3
77.5°	0.0
80°	2.1
82.5°	8.5
85°	6.4
87.5°	0.0
90°	0.0

(END OF REPORT)